


floor mounting - FTX - UC50 - UFC



Dimensions and technical information p. 125-128

NOTE : please use Cat. No. when placing your order

Pack	Cat. Nos.	FTX – base fixing plates
1	<div style="display: flex; justify-content: space-around;"> <div style="text-align: center;"> GS CM586180 </div> <div style="text-align: center;"> HR CM586183 </div> </div>	30 / 54 / 105 mm 35 → 600 mm For technical information see p. 125
1	<div style="text-align: center;"> 316L CM586184 </div>	

Pack	Cat. Nos.	UC50 – support cradles
1	<div style="display: flex; justify-content: space-around;"> <div style="text-align: center;"> GS CM586040 </div> <div style="text-align: center;"> GC CM586043 </div> </div>	30 → 54 mm 50 mm For technical information see p. 126
1	<div style="display: flex; justify-content: space-around;"> <div style="text-align: center;"> 304L CM586048 </div> <div style="text-align: center;"> 316L CM586044 </div> </div>	

Pack	Cat. No.	UFC – clamp unit
1	<div style="text-align: center;"> GS CM559220 </div>	30 → 150 mm 100 → 600 mm For technical information see p. 127-128 For CSNC cantilever arms, see p. 47 For RCSN support rails, see p. 50

Key: GS	Pre-galvanised	304L	Stainless steel 304 L
GC	Hot dip galvanised after manufacture	316L	Stainless steel 316 L
HR	High Resistance*		

* For more information on High Resistance finish p. 12-13, 150

For detailed information related to finishes, refer to p. 150-151

All dimensions (mm) are nominal