



Isolating switches RX³

from 40 A to 80 A



RCCBs RX³

residual current circuit breakers from 25 A to 63 A - AC & A types



Technical characteristics, **please consult the technical datasheet**

Conform to IEC 60947-3
 Grey handle
 AC 22 A
 Compatible with prong-type and fork type supply busbars
 Do not accept auxiliaries

Technical characteristics, **please consult the technical datasheet**

Conform to IEC 61008-1
 • AC type : detect AC component faults
 • A type : detect AC and DC component faults
 Compatible with prong-type and fork type supply busbars
 Do not accept auxiliaries

Pack	Cat.Nos	Isolating switches	Number of modules
6	4 193 24	2P - 400 V\sim Nominal rating In (A) 40	2
6	4 193 25	63	2
6	4 193 26	80	2
1	4 193 27	3P - 400 V\sim 40	3
1	4 193 28	63	3
1	4 193 29	80	3
1	4 193 30	4P - 400 V\sim 40	4
1	4 193 31	63	4
1	4 193 32	80	4

Pack	Cat.Nos	2-pole - 230 V \sim	In (A)	Number of modules
AC type				
		Sensitivity (mA)		
1	4 020 24	30	25	2
1	4 020 25	30	40	2
1	4 020 26	30	63	2
1	4 020 27	30	80	2
1	4 020 28	100	25	2
1	4 020 29	100	40	2
1	4 020 30	100	63	2
1	4 020 32	300	25	2
1	4 020 33	300	40	2
1	4 020 34	300	63	2
A type				
1	4 020 36	30	25	2
1	4 020 37	30	40	2
1	4 020 38	30	63	2
4-pole - 400 V\sim neutral on right-hand side				
AC type				
		Sensitivity (mA)	In (A)	Number of modules
1	4 020 62	30	25	4
1	4 020 63	30	40	4
1	4 020 64	30	63	4
1	4 020 66	100	25	4
1	4 020 67	100	40	4
1	4 020 68	100	63	4
1	4 020 70	300	25	4
1	4 020 71	300	40	4
1	4 020 72	300	63	4
A type				
1	4 020 74	30	25	4
1	4 020 75	30	40	4
1	4 020 76	30	63	4