


## Socket outlets and special modular supports



Allow insertion of supply busbars

Pack	Cat.Nos	10-16 A - 250 V~	
10	0 042 80	Automatic terminals <b>French standard</b> 2P + $\perp$ shuttered	Number of modules 2.5
10	0 042 85	<b>German standard</b> 2P + $\perp$ shuttered	2.5
5	0 042 91	<b>20 A - 400 V~</b> <b>French standard</b> 3P + $\perp$ shuttered	Number of modules 3.5
5	0 042 92	3P + N + $\perp$ shuttered	3.5
10	4 129 50	<b>Special supports</b> <b>Modular support for rail</b> Can be equipped with: - Arteor or Mosaic 2-module mechanisms - Osmoz control and signalling units with the special adaptor Cat.No 4 129 51 - other equipment when used with the blanking plate Cat.No 4 129 52	Number of modules 2.5
10	4 129 51	<b>Osmoz adaptor</b> Pre-drilled adaptor for mounting $\varnothing$ 22.5 mm control and signalling units on the modular support Cat.No 4 129 50	
10	4 129 52	<b>Blanking plate</b> Can be used as a blanking plate or for mounting different equipment on the modular support Cat.No 4 129 50 (e.g switches, lamps, printed circuits, potentiometers)	

## Transformers, buzzers and bells



Pack	Cat.Nos	Bell transformers						
1	4 130 91	$\triangle$ Conform to IEC / EN 61558-2-8 Protected against overloads and short circuits. In the event of an overload, switch "OFF" the power supply and allow the transformer to cool down before switching on again With label holders Wall or rail $\perp$ mounting (for 4 modules) Possibility for supply busbars to run through (Cat.No 4 130 91)						
1	4 130 92	<b>230 V/12 V - 8 V</b>						
		Secondary (V)	Rating (A)	Power (VA)	Number of modules			
1	4 130 91	12/8	0.66/1	8	2			
1	4 130 92	12/8	2/3	24	4			
1	4 130 93	<b>230 V/24 V - 12 V</b>						
		24/12	1/1.5	24 - 18	4			
1	4 130 96	<b>Safety transformers</b> Conform to IEC / EN 61558-2-6 Protected against overloads and short circuits. In the event of an overload, switch "OFF" the power supply and allow the transformer to cool down before switching on again Wall or rail $\perp$ mounting						
1	4 130 98	<b>230 V/12 or 24 V</b> (per coupling 2 x 12 V for Cat.No 4 130 98) Supplied with strip						
		P (VA)	No-load loss (W)	Voltage drop % Cos $\Phi$ = 1	Efficiency % Cos $\Phi$ = 1	Ucc (%)	I (A) primary loaded	Number of modules
1	4 130 96	25	2.5	29	66	23.3	0.142	5
1	4 130 98	63	4	15.7	75	13.6	0.33	5
10	0 041 01	<b>Buzzers and bells</b> 50 Hz AC - Connection by screw terminals, with label holder Allow insertion of supply busbars Caution: remove lamps from illuminated push-buttons when used with Cat.Nos 0 041 01						
10	0 041 07	<b>Bells</b>						
		Voltage (V~)	Power (VA)	Consum. (mA)	Acoustic power at 1 m (dB)	Number of modules		
10	0 041 01	8/12	4/5	360/420	80/84	1		
10	0 041 07	230	6	27	83	1		
10	0 041 13	<b>Buzzers</b>						
		230	6	27	73	1		