


## MCBs RX<sup>3</sup> 6000

thermal magnetic MCBs from 6 A to 63 A - C curve



Technical characteristics, **please consult the technical datasheet**

Conform to IEC 60898-1  
Do not accept auxiliaries, and add-on modules  
Compatible with prong-type supply busbars  
Breaking capacity:  
6000 - IEC 60898-1 - 230/400 V~  
6 kA - IEC 60947-2 - 230/400 V~  
10000 - IEC 60898-1 - 127/220 V~  
10 kA - IEC 60947-2 - 127/220 V~

Pack	Cat.Nos	Nominal rating I <sub>n</sub> (A)	Number of modules
	<b>C curve</b>		
12	4 198 37	6	1
12	4 198 38	10	1
12	4 198 40	16	1
12	4 198 41	20	1
12	4 198 42	25	1
12	4 198 43	32	1
12	4 198 44	40	1
12	4 198 45	50	1
12	4 198 46	63	1


Pack	Cat.Nos	Nominal rating I <sub>n</sub> (A)	Number of modules
	<b>C curve</b>		
6	4 198 70	6	2
6	4 198 71	10	2
6	4 198 73	16	2
6	4 198 74	20	2
6	4 198 75	25	2
6	4 198 76	32	2
6	4 198 77	40	2
6	4 198 78	50	2
6	4 198 79	63	2

Pack	Cat.Nos	Nominal rating I <sub>n</sub> (A)	Number of modules
	<b>C curve</b>		
4	4 198 81	6	3
4	4 198 82	10	3
4	4 198 84	16	3
4	4 198 85	20	3
4	4 198 86	25	3
4	4 198 87	32	3
4	4 198 88	40	3
4	4 198 89	50	3
4	4 198 90	63	3

Pack	Cat.Nos	Nominal rating I <sub>n</sub> (A)	Number of modules
	<b>C curve</b>		
3	4 199 14	6	4
3	4 199 15	10	4
3	4 199 17	16	4
3	4 199 18	20	4
3	4 199 19	25	4
3	4 199 20	32	4
3	4 199 21	40	4
3	4 199 22	50	4
3	4 199 23	63	4

## MCBs RX<sup>3</sup> 6000

thermal magnetic MCBs from 6 A to 63 A - B and C curves



Technical characteristics, **please consult the technical datasheet**

Conform to IEC 60898-1  
Do not accept auxiliaries, and add-on modules  
Compatible with prong-type and fork type supply busbars  
Breaking capacity:  
6000 - IEC 60898-1 - 230/400 V~  
6 kA - IEC 60947-2 - 230/400 V~  
10000 - IEC 60898-1 - 127/220 V~  
10 kA - IEC 60947-2 - 127/220 V~

Pack	Cat.Nos	Nominal rating I <sub>n</sub> (A)	Number of modules
	<b>B curve</b>		
	<b>C curve</b>		
12	4 191 33	6	1
12	4 191 34	10	1
12	4 191 35	13	1
12	4 191 36	16	1
12	4 191 37	20	1
12	4 191 38	25	1
12	4 191 39	32	1
12	4 191 40	40	1
12	4 191 41	50	1
12	4 191 42	63	1
12	4 191 99	6	1
12	4 192 00	10	1
12	4 192 01	13	1
12	4 192 02	16	1
12	4 192 03	20	1
12	4 192 04	25	1
12	4 192 05	32	1
12	4 192 06	40	1
12	4 192 07	50	1
12	4 192 08	63	1

Pack	Cat.Nos	Nominal rating I <sub>n</sub> (A)	Number of modules
	<b>B curve</b>		
	<b>C curve</b>		
6	4 191 55	6	2
6	4 191 56	10	2
6	4 191 57	13	2
6	4 191 58	16	2
6	4 191 59	20	2
6	4 191 60	25	2
6	4 191 61	32	2
6	4 191 62	40	2
6	4 191 63	50	2
6	4 191 64	63	2
6	4 192 21	6	2
6	4 192 22	10	2
6	4 192 23	13	2
6	4 192 24	16	2
6	4 192 25	20	2
6	4 192 26	25	2
6	4 192 27	32	2
6	4 192 28	40	2
6	4 192 29	50	2
6	4 192 30	63	2

Pack	Cat.Nos	Nominal rating I <sub>n</sub> (A)	Number of modules
	<b>B curve</b>		
	<b>C curve</b>		
4	4 191 66	6	3
4	4 191 67	10	3
4	4 191 68	13	3
4	4 191 69	16	3
4	4 191 70	20	3
4	4 191 71	25	3
4	4 191 72	32	3
4	4 191 73	40	3
4	4 191 74	50	3
4	4 191 75	63	3
4	4 192 32	6	3
4	4 192 33	10	3
4	4 192 34	13	3
4	4 192 35	16	3
4	4 192 36	20	3
4	4 192 37	25	3
4	4 192 38	32	3
4	4 192 39	40	3
4	4 192 40	50	3
4	4 192 41	63	3

Pack	Cat.Nos	Nominal rating I <sub>n</sub> (A)	Number of modules
	<b>C curve</b>		
3	4 192 55	10	4
3	4 192 56	13	4
3	4 192 57	16	4
3	4 192 58	20	4