

DRX™ 125

thermal magnetic MCCBs from 15 to 125 A



Dimensions and installation principle **p. 136**
 Technical characteristics and curves **p. 138**

For switching, control, isolation and protection of low-voltage electrical lines
 Can be fitted with auxiliaries (p. 133)

Supplied with:

- M5 terminal for $I_n \leq 50$ A and M8 range for $I_n > 50$ A
- Fixing screws
- Insulating shields (2 for 3P and 3 for 4P)

Fixed thermal and magnetic

Conform to IEC 60947-2, in compliance with NEMA

Pack	Cat.Nos		DRX 125
			Breaking capacity Icu 10 kA (415 V~)
	3P	4P	I_n
1	0 270 00	0 270 10	15 A
1	0 270 01	0 270 11	20 A
1	0 270 02	0 270 12	25 A
1	0 270 03	0 270 13	30 A
1	0 270 04	0 270 14	40 A
1	0 270 05	0 270 15	50 A
1	0 270 06	0 270 16	60 A
1	0 270 39	0 270 29	63 A
1	0 270 07	0 270 17	75 A
1	0 272 55	0 272 56	80 A
1	0 270 08	0 270 18	100 A
1	0 270 09	0 270 19	125 A
			Breaking capacity Icu 20 kA (415 V~)
			I_n
1	0 270 20	0 270 30	15 A
1	0 270 21	0 270 31	20 A
1	0 270 22	0 270 32	25 A
1	0 270 23	0 270 33	30 A
1	0 270 24	0 270 34	40 A
1	0 270 25	0 270 35	50 A
1	0 270 26	0 270 36	60 A
1	0 272 20	0 272 22	63 A
1	0 270 27	0 270 37	75 A
1	0 272 57	0 272 58	80 A
1	0 270 28	0 270 38	100 A
1	0 272 21	0 272 23	125 A
			Breaking capacity Icu 25 kA (220/240 V~)
			I_n
1	1P		15 A
1	0 270 40		20 A
1	0 270 41		25 A
1	0 270 42		30 A
1	0 270 43		40 A
1	0 270 44		50 A
1	0 270 45		60 A
1	0 270 46		75 A
1	0 270 47		100 A
			Breaking capacity Icu 36 kA (415 V~)
			I_n
1	2P		15 A
1	0 270 50		20 A
1	0 270 51		25 A
1	0 270 52		30 A
1	0 270 53		40 A
1	0 270 54		50 A
1	0 270 55		60 A
1	0 270 56		75 A
1	0 270 57		100 A
1	0 270 58		

Pack	Cat.Nos		DRX-I 125
1	6 671 39 6 671 59		Trip-free switches for on-load circuit breaking and isolation of low voltage electrical circuits 125 A
			Mounting on rail
20	0 271 89		Plates for fixing DRX 125 on DIN rail
12	0 271 90		For 1P
6	0 271 87		For 2P For 3P and 4P
			Rotary handles
1	0 271 76		Direct on DRX Standard (grey)
1	0 271 77		Vari-depth handle Comprising: connecting rod, bracket, drilling template, mounting accessories, door locking mechanism Standard (grey)
			Connection accessories
			Insulating shields Used to isolate the connection between each pole
1	3P	4P	Set of 2
1	0 271 81	0 271 82	Set of 3
			Sealable terminal shields
1	2P		Set of 2
1	3P	4P	Set of 2
1	0 271 83	0 271 84	
1	3P	4P	Cage terminals
1	0 271 70	0 271 72	Up to 50 A (inclusive)
1	0 271 71	0 271 73	From 60 to 100 A
1	0 272 52	0 272 53	For 125 A
1	0 271 92		Set of 60 pieces up to 50 A (inclusive)
1	0 271 93		Set of 60 pieces from 60 to 100 A
1	0 272 54		Set of 60 pieces 125 A
			Padlock for DRX 125 and 250
1	0 271 80		For locking on "OFF" position (up to 3 locks)