

## RCCBs TX<sup>3</sup> - residual current circuit breakers

from 25 A to 63 A - AC and A types



Technical characteristics, **please consult the technical datasheet**

Conform to IEC 61008-1

Compatible with prong-type supply busbars

- AC type : detect AC component faults
- A type : detect AC and DC component faults

Do not accept auxiliaries

Pack	Cat.Nos	2-pole - 230 V $\sim$		
		<b>AC type</b>		
		Sensitivity (mA)	In (A)	Number of modules
1	4 030 00	30	25	2
1	4 030 01	30	40	2
1	4 030 02	30	63	2
1	4 030 38	300	25	2
1	4 030 39	300	40	2
1	4 030 40	300	63	2
		<b>A type</b>		
1	4 030 35	30	25	2
1	4 030 36	30	40	2

Pack	Cat.Nos	4-pole - 400 V $\sim$		
		Neutral on left-hand side		
		<b>AC type</b>		
		Sensitivity (mA)	In (A)	Number of modules
1	4 030 04	30	25	4
1	4 030 05	30	40	4
1	4 030 06	30	63	4

Pack	Cat.Nos	4-pole - 400 V $\sim$		
		Neutral on right-hand side		
		<b>AC type</b>		
		Sensitivity (mA)	In (A)	Number of modules
1	4 030 08	30	25	4
1	4 030 09	30	40	4
1	4 030 10	30	63	4
1	4 030 42	300	25	4
1	4 030 43	300	40	4
1	4 030 44	300	63	4

## MCBs TX<sup>3</sup> 6000

thermal magnetic MCBs from 6 A to 63 A - C curve



Technical characteristics, **please consult the technical datasheet**

Conform to IEC 60898-1

Compatible with prong-type supply busbars

Breaking capacity:

**6000**- IEC 60898-1 - 230/400 V $\sim$

6 kA - IEC 60947-2 - 230/400 V $\sim$

Can be equipped with DX<sup>3</sup> signalling and remote tripping auxiliaries and motorised controls (p. 73-74)

Do not accept add-on modules

Pack	Cat.Nos	Single pole 230/400 V $\sim$	
		<b>C curve</b>	
		Nominal rating In (A)	Number of modules
10	4 035 74	6	1
10	4 035 75	10	1
10	4 035 76	16	1
10	4 035 77	20	1
10	4 035 78	25	1
10	4 035 79	32	1
10	4 035 80	40	1
10	4 035 81	50	1
10	4 035 82	63	1

Pack	Cat.Nos	Single pole + neutral 230 V $\sim$	
		Neutral on left-hand side	
		<b>C curve</b>	
		Nominal rating In (A)	Number of modules
5	4 035 84	6	2
5	4 035 85	10	2
5	4 035 86	16	2
5	4 035 87	20	2
5	4 035 88	25	2
5	4 035 89	32	2
5	4 035 90	40	2

Pack	Cat.Nos	2-pole 230/400 V $\sim$	
		<b>C curve</b>	
		Nominal rating In (A)	Number of modules
5	4 036 04	6	2
5	4 036 05	10	2
5	4 036 06	16	2
5	4 036 07	20	2
5	4 036 08	25	2
5	4 036 09	32	2
5	4 036 10	40	2
5	4 036 11	50	2
5	4 036 12	63	2

Pack	Cat.Nos	3-pole 400 V $\sim$	
		<b>C curve</b>	
		Nominal rating In (A)	Number of modules
1	4 036 14	6	3
1	4 036 15	10	3
1	4 036 16	16	3
1	4 036 17	20	3
1	4 036 18	25	3
1	4 036 19	32	3
1	4 036 20	40	3
1	4 036 21	50	3
1	4 036 22	63	3

Pack	Cat.Nos	4-pole 400 V $\sim$	
		<b>C curve</b>	
		Nominal rating In (A)	Number of modules
1	4 036 24	6	4
1	4 036 25	10	4
1	4 036 26	16	4
1	4 036 27	20	4
1	4 036 28	25	4
1	4 036 29	32	4
1	4 036 30	40	4
1	4 036 31	50	4
1	4 036 32	63	4

See the video

