

## DRX™ 125 HP

thermal magnetic MCCBs from 16 to 125 A



6 693 89

6 693 99

Dimensions and installation principle p. 150  
Technical characteristics and curves p. 152-153

For switching, control, isolation and protection of low-voltage electrical lines. Can be fitted with auxiliaries (p. 147). Supplied with: screw terminals, fixing screws, insulating shields (2 for 3P and 3 for 4P). Fixed thermal and magnetic  
Conform to IEC 60947-2

Pack	Cat.Nos		DRX 125 HP
	3P	4P	<b>Breaking capacity Icu 25 kA (415 V~)</b>
1	6 693 40	6 693 50	16 A
1	6 693 41	6 693 51	20 A
1	6 693 42	6 693 52	25 A
1	6 693 43	6 693 53	32 A
1	6 693 44	6 693 54	40 A
1	6 693 45	6 693 55	50 A
1	6 693 46	6 693 56	63 A
1	6 693 47	6 693 57	80 A
1	6 693 48	6 693 58	100 A
1	6 693 49	6 693 59	125 A
			<b>Breaking capacity Icu 36 kA (415 V~)</b>
1	6 693 60	6 693 70	16 A
1	6 693 61	6 693 71	20 A
1	6 693 62	6 693 72	25 A
1	6 693 63	6 693 73	32 A
1	6 693 64	6 693 74	40 A
1	6 693 65	6 693 75	50 A
1	6 693 66	6 693 76	63 A
1	6 693 67	6 693 77	80 A
1	6 693 68	6 693 78	100 A
1	6 693 69	6 693 79	125 A
			<b>Breaking capacity Icu 50 kA (415 V~)</b>
1	6 693 80	6 693 90	16 A
1	6 693 81	6 693 91	20 A
1	6 693 82	6 693 92	25 A
1	6 693 83	6 693 93	32 A
1	6 693 84	6 693 94	40 A
1	6 693 85	6 693 95	50 A
1	6 693 86	6 693 96	63 A
1	6 693 87	6 693 97	80 A
1	6 693 88	6 693 98	100 A
1	6 693 89	6 693 99	125 A

## DRX™ 125 HP adjustable

thermal magnetic MCCBs from 16 to 125 A



6 697 49

6 697 59

Dimensions and installation principle p. 150  
Technical characteristics and curves p. 152-153

For switching, control, isolation and protection of low-voltage electrical lines. Can be fitted with auxiliaries (p. 147). Supplied with: screw terminals, fixing screws, insulating shields (2 for 3P and 3 for 4P). Adjustable thermal  
Fixed magnetic  
Conform to IEC 60947-2

Pack	Cat.Nos		DRX 125 HP
	3P	4P	Thermal adjustable from 0.8 to 1 x In <b>Breaking capacity Icu 25 kA (415 V~)</b>
			In
1	6 697 00	6 697 10	16 A
1	6 697 01	6 697 11	20 A
1	6 697 02	6 697 12	25 A
1	6 697 03	6 697 13	32 A
1	6 697 04	6 697 14	40 A
1	6 697 05	6 697 15	50 A
1	6 697 06	6 697 16	63 A
1	6 697 07	6 697 17	80 A
1	6 697 08	6 697 18	100 A
1	6 697 09	6 697 19	125 A
			<b>Breaking capacity Icu 36 kA (415 V~)</b>
1	6 697 20	6 697 30	16 A
1	6 697 21	6 697 31	20 A
1	6 697 22	6 697 32	25 A
1	6 697 23	6 697 33	32 A
1	6 697 24	6 697 34	40 A
1	6 697 25	6 697 35	50 A
1	6 697 26	6 697 36	63 A
1	6 697 27	6 697 37	80 A
1	6 697 28	6 697 38	100 A
1	6 697 29	6 697 39	125 A
			<b>Breaking capacity Icu 50 kA (415 V~)</b>
1	6 697 40	6 697 50	16 A
1	6 697 41	6 697 51	20 A
1	6 697 42	6 697 52	25 A
1	6 697 43	6 697 53	32 A
1	6 697 44	6 697 54	40 A
1	6 697 45	6 697 55	50 A
1	6 697 46	6 697 56	63 A
1	6 697 47	6 697 57	80 A
1	6 697 48	6 697 58	100 A
1	6 697 49	6 697 59	125 A