

# Add-on modules DX<sup>3</sup>

for 1 module/pole DX<sup>3</sup> MCBs



4 104 01



4 104 71



4 105 55

Performance of DX<sup>3</sup> add-on modules **p. 76-77**

Conform to IEC 61009-1, IEC 62423 (F type)  
Voltage independent tripping except Cat.Nos 4 106 57/58/59

- AC type : detect AC components faults
  - A type : detect AC and DC component faults
  - F type (High immunity) : detect faults with AC and DC components, increased immunity to false tripping
- Detection of high frequency fault currents

For mounting on the right-hand side of 1 module per pole DX<sup>3</sup> MCBs

## Pack Cat.Nos 2-pole - 230 V~

Pack	Cat.Nos	Sensitivity (mA)	Nominal rating In (A)	Number of modules
<b>AC Type</b>				
1	4 104 01	30	40	2
1	4 104 02	30	63	2
1	4 104 13	300	40	2
1	4 104 14	300	63	2
1	4 104 24	300 selective	63	2
1	4 104 26	1000 selective	63	2
<b>A Type</b>				
1	4 104 28	30	40	2
1	4 104 29	30	63	2
1	4 104 31	300	40	2
1	4 104 32	300	63	2
<b>F type</b>				
1	4 104 35	30	63	2

## Pack Cat.Nos 3-pole - 400 V~

Pack	Cat.Nos	Sensitivity (mA)	Nominal rating In (A)	Number of modules
<b>AC Type</b>				
1	4 104 71	30	40	3
1	4 104 72	30	63	3
1	4 104 74	300	40	3
1	4 104 75	300	63	3
1	4 104 77	300 selective	63	3
<b>A Type</b>				
1	4 104 80	30	63	3
1	4 104 83	300	63	3
<b>F type</b>				
1	4 104 86	30	63	3

## Pack Cat.Nos 4-pole - 400 V~

Pack	Cat.Nos	Sensitivity (mA)	Nominal rating In (A)	Number of modules
<b>AC Type</b>				
1	4 104 99	30	40	3
1	4 105 00	30	63	3
1	4 105 11	300	40	3
1	4 105 12	300	63	3
1	4 105 21	300 selective	63	3
1	4 105 23	1000 selective	63	3
<b>A Type</b>				
1	4 105 25	30	40	3
1	4 105 26	30	63	3
1	4 105 28	300	40	3
1	4 105 29	300	63	3
1	4 105 31	300 selective	63	3
<b>F type</b>				
1	4 105 34	30	63	3
1	4 105 55	300 selective	63	3