

## Power contactors without handle CX<sup>3</sup>

from 16 A to 63 A



4 125 05

4 125 35


Technical characteristics p. 95

Conform to IEC/EN 61095  
Space for power supply busbar on top (up to 25 A)

Pack	Cat.Nos	Power contactors with 24 V~ coil		
		<b>2-pole - 250 V~</b>		
1	4 125 03	I max 16 A	Connection 	Type of contact N/C + N/O  Number of modules 1
1	4 125 05	25 A		2 N/O  1
		<b>4-pole - 400 V~</b>		
1	4 125 10	25 A		4 N/O  2
1	4 125 09	25 A		2 N/C + 2 N/O  2

Pack	Cat.Nos	Power contactors with 230 V~ coil		
		<b>2-pole - 250 V~</b>		
4	4 125 21	I max 16 A	Connection 	Type of contact N/C + N/O  Number of modules 1
10	4 125 23	25 A		2 N/O 1
1	4 125 27	63 A		2 N/O 2
1	4 125 24	25 A		2 N/C 1
		<b>4-pole - 400 V~</b>		
5	4 125 35	25 A		4 N/O 2
1	4 125 41	63 A		4 N/O 3
1	4 125 36	25 A		4 N/C 2
1	4 125 33	25 A		2 N/C + 2 N/O 2

## Auxiliaries for contactors CX<sup>3</sup>



4 124 29

4 124 31

Pack	Cat.Nos	Signalling auxiliaries for contactors			
		Auxiliary changeover switch for all CX <sup>3</sup> contactors Used to signal the position status of the contacts on the product to which it is connected			
		<b>For 1 module contactors 16 A to 25 A</b> Maximum 2 auxiliary devices per contactor Fitted on left-hand side of contactor			
1	4 124 29	I max 5 A	Voltage 250 V~	Contact N/C + N/O	Number of modules 0.5
		<b>For 2 module contactors 25 A</b> Maximum 2 auxiliary devices per contactor Fitted on left-hand side of contactor			
1	4 124 30	5 A	250 V~	N/C + N/O	0.5
		<b>For 40 and 63 A contactors</b> Maximum 1 auxiliary device per contactor Fitted on left-hand side of contactor			
1	4 124 31	5 A	250 V~	N/C + N/O	0.5