

# DPX<sup>3</sup> 250

S2 electronic release MCCBs from 40 to 250 A - fixing on rail or on plate



4 203 69



4 203 25

Dimensions **p. 188**  
 Electrical characteristics **p. 189**

Can be mounted on rail or on plate in XL<sup>3</sup> and XL<sup>3</sup> S cabinets and enclosures  
 MCCBs for switching, control isolation and protection of low voltage electrical lines  
 Supplied with fixing screws, connection plates for bars and cable lugs and insulated shileds (phase barriers)  
 Can be fitted with cage terminals 120 mm<sup>2</sup> max. (flexible cable) or 150 mm<sup>2</sup> max. rigid cable (p. 164)  
 and with DPX<sup>3</sup> 160 and 250 common auxiliaries and accessories (p. 165)  
 Conform to IEC 60947-2

Pack	Cat.Nos		MCCBs S2 electronic release - fixed version
	3P	4P	
1	4 203 02	4 203 12	In (A) 40
1	4 203 05	4 203 15	100
1	4 203 07	4 203 17	160
1	4 203 09	4 203 19	250
			<b>Breaking capacity I<sub>cu</sub> 36 kA (400 V<sub>~</sub>)</b>
1	4 203 32	4 203 42	40
1	4 203 35	4 203 45	100
1	4 203 37	4 203 47	160
1	4 203 39	4 203 49	250
			<b>Breaking capacity I<sub>cu</sub> 50 kA (400 V<sub>~</sub>)</b>
1	4 203 62	4 203 72	40
1	4 203 65	4 203 75	100
1	4 203 67	4 203 77	160
1	4 203 69	4 203 79	250

Pack	Cat.Nos	MCCBs S2 electronic release with electronic earth leakage module - fixed version
	4P	In (A)
1	4 203 22	40
1	4 203 25	100
1	4 203 27	160
1	4 203 29	250
		<b>Breaking capacity I<sub>cu</sub> 36 kA (400 V<sub>~</sub>)</b>
1	4 203 52	40
1	4 203 55	100
1	4 203 57	160
1	4 203 59	250
		<b>Breaking capacity I<sub>cu</sub> 50 kA (400 V<sub>~</sub>)</b>
1	4 203 82	40
1	4 203 85	100
1	4 203 87	160
1	4 203 89	250