

DPX³ 250

S2 electronic release MCCBs from 40 to 250 A - fixing on rail or on plate (continued)



Dimensions **p. 188**
 Electrical characteristics **p. 189**

Can be mounted on rail or on plate in XL³ and XL³ S cabinets and enclosures
 MCCBs for switching, control isolation and protection of low voltage electrical lines
 Supplied with fixing screws, connection plates for bars and cable lugs and insulated shileds (phase barriers)
 Can be fitted with cage terminals 120 mm² max. (flexible cable) or 150 mm² max. rigid cable (p. 164)
 and with DPX³ 160 and 250 common auxiliaries and accessories (p. 165)
 Conform to IEC 60947-2

Pack	Cat.Nos		
			MCCBs S2 electronic release with energy metering central unit - fixed version
			Protection against overloads: Ir adjustable from 0.4 to 1 x In tr adjustable from 3 to 15s Protection against short circuits: Isd adjustable from 1.5 to 10 x Ir tsd adjustable from 0 to 0.5s Integrated energy metering central unit with LCD screen; currents, voltage, frequency, power, energy and harmonics
			Breaking capacity Icu 25 kA (400 V~)
	3P	4P	In (A)
1	4 204 02	4 204 12	40
1	4 204 05	4 204 15	100
1	4 204 07	4 204 17	160
1	4 204 09	4 204 19	250
			Breaking capacity Icu 36 kA (400 V~)
1	4 204 32	4 204 42	40
1	4 204 35	4 204 45	100
1	4 204 37	4 204 47	160
1	4 204 39	4 204 49	250
			Breaking capacity Icu 50 kA (400 V~)
1	4 204 62	4 204 72	40
1	4 204 65	4 204 75	100
1	4 204 67	4 204 77	160
1	4 204 69	4 204 79	250

Pack	Cat.Nos	
		MCCBs S2 electronic release with energy metering central unit and electronic earth leakage module - fixed version
		Protection against overloads: Ir adjustable from 0.4 to 1 x In tr adjustable from 3 to 15s Protection against short circuits: Isd adjustable from 1.5 to 10 x Ir tsd adjustable from 0 to 0.5s Equipped with earth leakage module with LCD screen Adjustable sensitivity: 0.03 - 0.3 - 1 - 3 A Adjustable tripping: 0 - 0.3 - 1 - 3s (with 0.03 A possible only 0s) Integrated energy metering central unit with LCD screen; currents, voltage, frequency, power, energy and harmonics
		Breaking capacity Icu 25 kA (400 V~)
	4P	In (A)
1	4 204 22	40
1	4 204 25	100
1	4 204 27	160
1	4 204 29	250
		Breaking capacity Icu 36 kA (400 V~)
1	4 204 52	40
1	4 204 55	100
1	4 204 57	160
1	4 204 59	250
		Breaking capacity Icu 50 kA (400 V~)
1	4 204 82	40
1	4 204 85	100
1	4 204 87	160
1	4 204 89	250