


## Programmable time switches

with analogue dial



Programmed via captive segment  
 Power supply: 230 V $\sim$  - 50/60 Hz  
 3-position override switch "ON-AUTO-OFF" on front panel  
 Manual changeover to summer/winter time  
 1 outlet 16 A - 250 V $\sim$  -  $\mu$  cos  $\varphi$  = 1


Pack	Cat.Nos	Daily programme	Number of modules
1	4 127 80	1 segment = 15 minutes Accuracy: $\pm$ 5 minutes <b>Vertical dial</b> Minimum switching time: 15 minutes N/O contact Without working reserve	1
1	4 127 90	With 100 h working reserve	1
1	4 128 12	<b>Horizontal dial</b> Minimum switching time: 15 minutes Changeover switch Without working reserve	3
1	4 128 13	With 100 h working reserve	3
1	4 127 94	<b>Weekly programme</b> 1 segment = 2 hours Accuracy: $\pm$ 30 minutes <b>Vertical dial</b> Minimum switching time: 2 hours N/O contact With 100 h working reserve	1
1	4 127 95	<b>Horizontal dial</b> Minimum switching time: 4 hours Changeover switch With 100 h working reserve	3

## Programmable time switches


with analogue dial - technical characteristics

### Diagrams

Cat.Nos 4 127 80/90/94



Cat.Nos 4 128 12/13, 4 127 95



### Technical characteristics

Cat.Nos	Programme	Segment	Min. switching time	Working reserve	16 A output via contact		Nb of modules
					N/O	Chang. S.	
4 128 12	24 h	15 min	30 min	without	-	1	3
4 128 13	24 h	15 min	30 min	100 h	-	1	3
4 127 80	24 h	15 min	15 min	without	1	-	1
4 127 90	24 h	15 min	15 min	100 h	1	-	1
4 127 94	7 d	2 h	2 h	100 h	1	-	1
4 127 95	7 d	2 h	4 h	100 h	-	1	3