

# DPX<sup>3</sup> 125 HP

thermal magnetic release MCCBs from 16 to 125 A - fixing on plate



4 236 49



4 236 59



4 236 39

Dimensions **p. 190**  
 Electrical characteristics **p. 193**

Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines

Can be fitted with auxiliaries (p. 175)

Supplied with: screws for connections, fixing screws and insulated shields (phase barriers)

Can be fitted with cage terminals 120 mm<sup>2</sup> max. (flexible cable) or 150 mm<sup>2</sup> max. rigid cable (p. 169)

Conform to IEC 60947-2 - Sealable adjustment.

Can be mounted on plate in XL<sup>3</sup> and XL<sup>3</sup> S cabinets and enclosures

Pack	Cat.Nos		MCCBs thermal magnetic release - fixed version
			<b>Breaking capacity Icu 36 kA (400 V<sub>~</sub>)</b>
			In (A)
	3P	4P	
1	4 236 00	4 236 10	16
1	4 236 01	4 236 11	20
1	4 236 02	4 236 12	25
1	4 236 03	4 236 13	32
1	4 236 04	4 236 14	40
1	4 236 05	4 236 15	50
1	4 236 06	4 236 16	63
1	4 236 07	4 236 17	80
1	4 236 08	4 236 18	100
1	4 236 09	4 236 19	125
			<b>Breaking capacity Icu 50 kA (400 V<sub>~</sub>)</b>
1	4 236 40	4 236 50	16
1	4 236 41	4 236 51	20
1	4 236 42	4 236 52	25
1	4 236 43	4 236 53	32
1	4 236 44	4 236 54	40
1	4 236 45	4 236 55	50
1	4 236 46	4 236 56	63
1	4 236 47	4 236 57	80
1	4 236 48	4 236 58	100
1	4 236 49	4 236 59	125
			<b>Breaking capacity Icu 70 kA (400 V<sub>~</sub>)</b>
1	4 236 80	4 236 90	16
1	4 236 81	4 236 91	20
1	4 236 82	4 236 92	25
1	4 236 83	4 236 93	32
1	4 236 84	4 236 94	40
1	4 236 85	4 236 95	50
1	4 236 86	4 236 96	63
1	4 236 87	4 236 97	80
1	4 236 88	4 236 98	100
1	4 236 89	4 236 99	125
			<b>Breaking capacity Icu 100 kA (400 V<sub>~</sub>)</b>
1	4 237 00	4 237 10	16
1	4 237 01	4 237 11	20
1	4 237 02	4 237 12	25
1	4 237 03	4 237 13	32
1	4 237 04	4 237 14	40
1	4 237 05	4 237 15	50
1	4 237 06	4 237 16	63
1	4 237 07	4 237 17	80
1	4 237 08	4 237 18	100
1	4 237 09	4 237 19	125

Pack	Cat.Nos	MCCBs thermal magnetic release with electronic earth leakage module - fixed version
		Equipped with earth leakage module Adjustable sensitivity: 0.03 - 0.3 - 1 - 3 A Adjustable tripping: 0 - 0.3 - 1 - 3 s (with 0.03 A possible only 0 s)
		<b>Breaking capacity Icu 36 kA (400 V<sub>~</sub>)</b>
		In (A)
	4P	
1	4 236 30	16
1	4 236 31	20
1	4 236 32	25
1	4 236 33	32
1	4 236 34	40
1	4 236 35	50
1	4 236 36	63
1	4 236 37	80
1	4 236 38	100
1	4 236 39	125
		<b>Breaking capacity Icu 50 kA (400 V<sub>~</sub>)</b>
1	4 236 70	16
1	4 236 71	20
1	4 236 72	25
1	4 236 73	32
1	4 236 74	40
1	4 236 75	50
1	4 236 76	63
1	4 236 77	80
1	4 236 78	100
1	4 236 79	125