

DRX™ 630

thermal magnetic MCCBs from 320 to 630 A



DRX™ 630 adjustable

thermal magnetic MCCBs from 320 to 630 A



0 272 45



0 272 49



6 676 51



Dimensions **p. 142**
Technical characteristics and curves **p. 144**

For switching, control, isolation and protection of low-voltage electrical lines
Can be fitted with auxiliaries (p. 135)

Supplied with:

- Screw terminals
- Fixing screws
- Insulating shields (2 for 3P and 3 for 4P)

Fixed thermal and magnetic
Conform to IEC 60947-2

Pack	Cat.Nos		DRX 630
	3P	4P	
			Breaking capacity I_{cu} 36 kA (415 V_~)
1	0 272 34	0 272 38	In
1	0 272 35	0 272 39	320 A
1	0 272 36	0 272 40	400 A
1	0 272 37	0 272 41	500 A
			630 A
			Breaking capacity I_{cu} 50 kA (415 V_~)
1	0 272 42	0 272 46	In
1	0 272 43	0 272 47	320 A
1	0 272 44	0 272 48	400 A
1	0 272 45	0 272 49	500 A
			630 A



Dimensions **p. 142**
Technical characteristics and curves **p. 144**

For switching, control, isolation and protection of low-voltage electrical lines
Can be fitted with auxiliaries (p. 135)

Supplied with:

- Screw terminals
- Fixing screws
- Insulating shields (2 for 3P and 3 for 4P)

Adjustable thermal and magnetic
Conform to IEC 60947-2

Pack	Cat.Nos		DRX 630
	3P	4P	
			Thermal adjustable from 0.8 to 1 x I _n Magnetic adjustable from 5 to 10 x I _n
			Breaking capacity I_{cu} 36 kA (415 V_~)
1	6 676 50	6 676 54	In
1	6 676 51	6 676 55	320 A
1	6 676 52	6 676 56	400 A
1	6 676 53	6 676 57	500 A
			630 A
			Breaking capacity I_{cu} 50 kA (415 V_~)
1	6 676 58	6 676 62	In
1	6 676 59	6 676 63	320 A
1	6 676 60	6 676 64	400 A
1	6 676 61	6 676 65	500 A
			630 A