

DPX³ 250

thermal magnetic release MCCBs from 100 to 250 A - fixing on rail or on plate



4 202 05



4 202 25

Dimensions **p. 188**
 Electrical characteristics **p. 189**

Can be mounted on rail or on plate in XL³ and XL³ S cabinets and enclosures
 MCCBs for switching, control isolation and protection of low voltage electrical lines
 Supplied with fixing screws, connection plates for bars and cable lugs and insulated shileds (phase barriers)
 Can be fitted with cage terminals 120 mm² max. (flexible cable) or 150 mm² max. rigid cable (p. 164)
 and with DPX³ 160 and 250 common auxiliaries and accessories (p. 165)
 Conform to IEC 60947-2

Pack	Cat.Nos		
			MCCBs thermal magnetic release - fixed version
			Thermal adjustable from 0.8 to 1 In Magnetic adjustable from 5 to 10 In
			Breaking capacity Icu 25 kA (400 V\sim)
			In (A)
	3P	4P	
1	4 202 05	4 202 15	100
1	4 202 07	4 202 17	160
1	4 202 08	4 202 18	200
1	4 202 09	4 202 19	250
			Breaking capacity Icu 36 kA (400 V\sim)
1	4 202 35	4 202 45	100
1	4 202 37	4 202 47	160
1	4 202 38	4 202 48	200
1	4 202 39	4 202 49	250
			Breaking capacity Icu 50 kA (400 V\sim)
1	4 202 65	4 202 75	100
1	4 202 67	4 202 77	160
1	4 202 68	4 202 78	200
1	4 202 69	4 202 79	250

Pack	Cat.Nos	
		MCCBs thermal magnetic release with electronic earth leakage module - fixed version
		Thermal adjustable from 0.8 to 1 In Magnetic adjustable from 5 to 10 In Equipped with earth leakage module with LCD screen Adjustable sensitivity: 0.03 - 0.3 - 1 - 3 A Adjustable tripping: 0 - 0.3 - 1 - 3s (with 0.03 A possible only 0s)
		Breaking capacity Icu 25 kA (400 V\sim)
		In (A)
	4P	
1	4 202 25	100
1	4 202 27	160
1	4 202 28	200
1	4 202 29	250
		Breaking capacity Icu 36 kA (400 V\sim)
1	4 202 55	100
1	4 202 57	160
1	4 202 58	200
1	4 202 59	250
		Breaking capacity Icu 50 kA (400 V\sim)
1	4 202 85	100
1	4 202 87	160
1	4 202 88	200
1	4 202 89	250

DPX³ I trip-free switches
p. 186

DPX³ magnetic release only MCCBs
p. 186-187