

# Air circuit breakers DMX<sup>3</sup> 2500 and 4000

from 630 A to 4000 A



0 283 96 + 0 283 06



0 284 17 + 0 283 04



0 284 56 + 0 283 04

Dimensions **p. 228 to 231**  
 Electrical characteristics **p. 233 to 235**

Automatic air circuit breakers must be equipped with electronic protection unit (p. 217), imperatively ordered together for factory assembly  
 Please ask for DMX<sup>3</sup> order form  
 Conform to IEC 60947-2

Pack	Cat.Nos		Fixed version
			Supplied with - 1 fault signalling contact NO/NC - 2 auxiliary contacts: NO/NC - rear terminals for horizontal connection with bars - door sealing
			<b>DMX<sup>3</sup> - N 2500</b> Breaking capacity Icu 50 kA (415 V <sub>N</sub> )
			Frame 2500
	3P	4P	In(A)
1	0 283 60	0 283 70	630
1	0 283 61	0 283 71	800
1	0 283 62	0 283 72	1000
1	0 283 63	0 283 73	1250
1	0 283 64	0 283 74	1600
1	0 283 65	0 283 75	2000
1	0 283 66	0 283 76	2500
			<b>DMX<sup>3</sup> - H 2500</b> Breaking capacity Icu 65 kA (415 V <sub>N</sub> )
1	0 283 80	0 283 90	630
1	0 283 81	0 283 91	800
1	0 283 82	0 283 92	1000
1	0 283 83	0 283 93	1250
1	0 283 84	0 283 94	1600
1	0 283 85	0 283 95	2000
1	0 283 86	0 283 96	2500
			<b>DMX<sup>3</sup> - L 2500</b> Breaking capacity Icu 100 kA (415 V <sub>N</sub> )
			Frame 4000
	3P	4P	In(A)
1	0 284 00	0 284 10	630
1	0 284 01	0 284 11	800
1	0 284 02	0 284 12	1000
1	0 284 03	0 284 13	1250
1	0 284 04	0 284 14	1600
1	0 284 05	0 284 15	2000
1	0 284 06	0 284 16	2500
			<b>DMX<sup>3</sup> - N 4000</b> Breaking capacity Icu 50 kA (415 V <sub>N</sub> )
1	0 283 67	0 283 77	3200
1	0 283 68	0 283 78	4000
			<b>DMX<sup>3</sup> - H 4000</b> Breaking capacity Icu 65 kA (415 V <sub>N</sub> )
1	0 283 87	0 283 97	3200
1	0 283 88	0 283 98	4000
			<b>DMX<sup>3</sup> - L 4000</b> Breaking capacity Icu 100 kA (415 V <sub>N</sub> )
1	0 284 07	0 284 17	3200
1	0 284 08	0 284 18	4000

Pack	Cat.Nos		Draw-out version
			Supplied with: - 1 fault signalling contact NO/NC - 2 auxiliary contacts: NO/NC - draw-out base and kit - flat rear terminals for connection with bars - door sealing
			<b>DMX<sup>3</sup> - N 2500</b> Breaking capacity Icu 50 kA (415 V <sub>N</sub> )
			Frame 2500
	3P	4P	In(A)
1	0 284 20	0 284 30	630
1	0 284 21	0 284 31	800
1	0 284 22	0 284 32	1000
1	0 284 23	0 284 33	1250
1	0 284 24	0 284 34	1600
1	0 284 25	0 284 35	2000
1	0 284 26	0 284 36	2500
			<b>DMX<sup>3</sup> - H 2500</b> Breaking capacity Icu 65 kA (415 V <sub>N</sub> )
1	0 284 40	0 284 50	630
1	0 284 41	0 284 51	800
1	0 284 42	0 284 52	1000
1	0 284 43	0 284 53	1250
1	0 284 44	0 284 54	1600
1	0 284 45	0 284 55	2000
1	0 284 46	0 284 56	2500
			<b>DMX<sup>3</sup> - L 2500</b> Breaking capacity Icu 100 kA (415 V <sub>N</sub> )
			Frame 4000
	3P	4P	In(A)
1	0 284 60	0 284 70	630
1	0 284 61	0 284 71	800
1	0 284 62	0 284 72	1000
1	0 284 63	0 284 73	1250
1	0 284 64	0 284 74	1600
1	0 284 65	0 284 75	2000
1	0 284 66	0 284 76	2500
			<b>DMX<sup>3</sup> - N 4000</b> Breaking capacity Icu 50 kA (415 V <sub>N</sub> )
1	0 284 27	0 284 37	3200
1	0 284 28	0 284 38	4000
			<b>DMX<sup>3</sup> - H 4000</b> Breaking capacity Icu 65 kA (415 V <sub>N</sub> )
1	0 284 47	0 284 57	3200
1	0 284 48	0 284 58	4000
			<b>DMX<sup>3</sup> - L 4000</b> Breaking capacity Icu 100 kA (415 V <sub>N</sub> )
1	0 284 67	0 284 77	3200
1	0 284 68	0 284 78	4000

Old range DMX<sup>3</sup> 2500/4000/6300  
**p. 224**

Retrofit kits from DMX to DMX<sup>3</sup>  
**available on request**

Red catalogue numbers: New products