

DPX³ 1600

S10 configurable electronic release MCCBs from 630 to 1600 A - fixing on plate

January 2024



Dimensions **p. 196-197**
 Electrical characteristics **p. 198**

Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines
 Can be fitted with auxiliaries (p. 184)
 Can be used with residual current relays (p. 185)
 Supplied complete with:
 - connection plates for bars
 - insulated shields (phase barriers)
 Conform to IEC 60947-2 - Sealable adjustment
 Can be mounted on plate in XL³ and XL³ S cabinets and enclosures

Pack	Cat.Nos		
			MCCBs S10 configurable electronic release fixed version
			Adjustment of I_r , I_{sd} , I_i , I_g , t_r , t_{sd} , t_g directly on the MCCB or via software/App (p. 198) For connection to the App add a Bluetooth communication key Cat.No 0 283 10 (p. 184) Green indicator lamp Connector for test unit Logical selectivity 4P version: adjustment of neutral on front panel or by software or App
			Breaking capacity Icu 36 kA (400 V~)
	3P	4P	I_n (A)
1	4 229 00	4 229 01	500
1	4 229 20	4 229 25	630
1	4 229 21	4 229 26	800
1	4 229 22	4 229 27	1000
1	4 229 23	4 229 28	1250
1	4 229 24	4 229 29	1600
			Breaking capacity Icu 50 kA (400 V~)
1	4 229 02	4 229 03	500
1	4 229 30	4 229 35	630
1	4 229 31	4 229 36	800
1	4 229 32	4 229 37	1000
1	4 229 33	4 229 38	1250
1	4 229 34	4 229 39	1600
			Breaking capacity Icu 70 kA (400 V~)
1	4 229 04	4 229 05	500
1	4 229 40	4 229 45	630
1	4 229 41	4 229 46	800
1	4 229 42	4 229 47	1000
1	4 229 43	4 229 48	1250
1	4 229 44	4 229 49	1600
			Breaking capacity Icu 100 kA (400 V~)
1	4 229 06	4 229 07	500
1	4 229 50	4 229 55	630
1	4 229 51	4 229 56	800
1	4 229 52	4 229 57	1000
1	4 229 53	4 229 58	1250

Pack	Cat.Nos		
			MCCBs S10 configurable electronic release with energy metering central unit fixed version
			Adjustment of I_r , I_{sd} , I_i , I_g , t_r , t_{sd} , t_g directly on the MCCB or via software/App (p. 198) For connection to the App add a Bluetooth communication key Cat.No 0 283 10 (p. 184) Green indicator lamp Connector for test unit Logical selectivity 4P version: adjustment of neutral on front panel or by software or App For correct operation and power supply of metering function, see p. 184
			Breaking capacity Icu 36 kA (400 V~)
	3P	4P	I_n (A)
1	4 229 08	4 229 09	500
1	4 229 60	4 229 65	630
1	4 229 61	4 229 66	800
1	4 229 62	4 229 67	1000
1	4 229 63	4 229 68	1250
1	4 229 64	4 229 69	1600
			Breaking capacity Icu 50 kA (400 V~)
1	4 229 10	4 229 11	500
1	4 229 70	4 229 75	630
1	4 229 71	4 229 76	800
1	4 229 72	4 229 77	1000
1	4 229 73	4 229 78	1250
1	4 229 74	4 229 79	1600
			Breaking capacity Icu 70 kA (400 V~)
1	4 229 12	4 229 13	500
1	4 229 80	4 229 85	630
1	4 229 81	4 229 86	800
1	4 229 82	4 229 87	1000
1	4 229 83	4 229 88	1250
1	4 229 84	4 229 89	1600
			Breaking capacity Icu 100 kA (400 V~)
1	4 229 14	4 229 15	500
1	4 229 90	4 229 95	630
1	4 229 91	4 229 96	800
1	4 229 92	4 229 97	1000
1	4 229 93	4 229 98	1250