

DPX³-I trip-free switches

160 to 1600 A



Dimensions p. 188, 190-192 and 194-197

Trip-free switches for on-load circuit breaking and isolation of low voltage electrical circuits
 Can be associated to earth leakage modules or to corresponding DPX³ residual current relays
 Conform to IEC 60947-3
 Category of use AC 23 A
 Connection identical to corresponding DPX³

Pack	Cat.Nos	DPX ³ -I 160
1	3P 4 201 98 4P 4 201 99	In (A) 160 Mounting on rail with plate Cat.No 4 210 71 (p. 160)
1	4P with earth leakage module 4 201 97	160 Mounting on rail with plate Cat.No 4 210 73 (p. 160)
1	3P 4 202 99 4P 4 203 00	In (A) 250 Mounting on rail with plate Cat.No 4 210 72 (p. 164)
1	4P with earth leakage module 4 202 98	250 Mounting on rail with plate Cat.No 4 210 74 (p. 164)
1	3P 4 231 84 4P 4 231 85	In (A) 125
1	4 231 87	125 with earth leakage module
1	3P 4 231 88 4P 4 231 89	In (A) 160
1	4 231 91	160 with earth leakage module
1	3P 4 231 80 4P 4 231 81	In (A) 250
1	4 231 83	250 with earth leakage module
1	3P 4 222 16 4P 4 222 18	In (A) 400
1	4 222 17 4 222 19	630
1	3P 4 224 90 4P 4 224 94	In (A) 630
1	4 224 91 4 224 95	800
1	4 224 92 4 224 96	1250
1	4 224 93 4 224 97	1600

DPX³ magnetic release only

MCCBs from 16 to 1250 A for motor protection



Dimensions p. 188

Moulded case MCCBs for switching, control isolation and protection of three-phase motors
 Can be fitted with auxiliaries (p. 165)
 Supplied with: fixing screws and insulated shields (phase barriers)
 Conform to IEC 60947-2

Pack	Cat.Nos	DPX ³ 160
		Magnetic fixed Can be mounted on rail plate in XL ³ and XL ³ S cabinets and enclosures Supplied with cage terminals 70 mm ² max. flexible cable or 95 mm ² max. rigid cable with accessories Breaking capacity Icu 16 kA (400 V\sim)
	3P	In (A)
1	4 207 10	16
1	4 207 11	25
1	4 207 12	50
1	4 207 13	63
		Breaking capacity Icu 25 kA (400 V\sim)
1	4 207 14	16
1	4 207 15	25
1	4 207 16	50
1	4 207 17	63
		DPX³ 250
		Magnetic fixed Can be mounted on rail plate in XL ³ and XL ³ S cabinets and enclosures Supplied with cage terminals 95 mm ² max. flexible cable or 120 mm ² max. rigid cable with accessories Breaking capacity Icu 36 kA (400 V\sim)
	3P	In (A)
1	4 207 18	100
1	4 207 19	160
1	4 207 20	200
1	4 207 21	250
	3P+N	250
1	8 002 49	250
	4P	250
1	8 002 59	250
	3P	Breaking capacity Icu 70 kA (400 V\sim)
1	4 207 22	100
1	4 207 23	160
1	4 207 24	200
1	4 207 25	250