

## DMX<sup>3</sup> 2500, 4000 and 6300 old range

selection table

DMX <sup>3</sup>		ACBs TO BE EQUIPPED WITH MP4 OR MP6 PROTECTION UNITS			
Breaking capacity Icu (kA)	In (A)	Fixed version		Draw-out version	
		3P	4P	3P	4P
50 kA	<b>Frame 2500</b>				
	800	0 286 21	0 286 31	0 287 21	0 287 31
	1000	0 286 22	0 286 32	0 287 22	0 287 32
	1250	0 286 23	0 286 33	0 287 23	0 287 33
	1600	0 286 24	0 286 34	0 287 24	0 287 34
	2000	0 286 25	0 286 35	0 287 25	0 287 35
	2500	0 286 26	0 286 36	0 287 26	0 287 36
	<b>Frame 4000</b>				
	3200	0 286 27	0 286 37	0 287 27	0 287 37
	4000	0 286 28	0 286 38	0 287 28	0 287 38
65 kA	<b>Frame 2500</b>				
	800	0 286 41	0 286 51	0 287 41	0 287 51
	1000	0 286 42	0 286 52	0 287 42	0 287 52
	1250	0 286 43	0 286 53	0 287 43	0 287 53
	1600	0 286 44	0 286 54	0 287 44	0 287 54
	2000	0 286 45	0 286 55	0 287 45	0 287 55
	2500	0 286 46	0 286 56	0 287 46	0 287 56
	<b>Frame 4000</b>				
	3200	0 286 47	0 286 57	0 287 47	0 287 57
	4000	0 286 48	0 286 58	0 287 48	0 287 58
100 kA	<b>Frame 4000</b>				
	800	0 286 61	0 286 71	0 287 61	0 287 71
	1000	0 286 62	0 286 72	0 287 62	0 287 72
	1250	0 286 63	0 286 73	0 287 63	0 287 73
	1600	0 286 64	0 286 74	0 287 64	0 287 74
	2000	0 286 65	0 286 75	0 287 65	0 287 75
	2500	0 286 66	0 286 76	0 287 66	0 287 76
	3200	0 286 67	0 286 77	0 287 67	0 287 77
	4000	0 286 68	0 286 78	0 287 68	0 287 78
	<b>Frame 6300</b>				
5000	0 289 50	0 289 60	0 289 52	0 289 62	
6300	0 289 51	0 289 61	0 289 53	0 289 63	
MP4 protection units	LI	0 288 00			
	LSI	0 288 01			
	LSIg	0 288 02			
MP6 protection units	LSI	0 288 03			
	LSIg	0 288 04			
Communication option for MP4 protection units					0 288 05
External auxiliary power supply (input 24 V <sub>DC</sub> )					0 288 06
Programmable output option for MP4 protection units					0 288 12
External neutral for DMX <sup>3</sup> 2500 and 4000					0 288 11
External neutral for DMX <sup>3</sup> 6300					0 288 10

## DMX<sup>3</sup> 4000-1000 V<sub>~</sub> / DMX<sup>3</sup>-I 2500, 4000 and 6300 old range - selection table

DMX <sup>3</sup> 4000 1000 V <sub>~</sub>		ACBs TO BE EQUIPPED WITH MP4 PROTECTION UNITS			
Breaking capacity Icu (kA)	In (A)	Fixed version		Draw-out version	
		3P	4P	3P	4P
50 kA	<b>Frame 4000</b>				
	630	0 285 00	0 285 10	0 285 20	0 285 30
	800	0 285 01	0 285 11	0 285 21	0 285 31
	1000	0 285 02	0 285 12	0 285 22	0 285 32
	1250	0 285 03	0 285 13	0 285 23	0 285 33
	1600	0 285 04	0 285 14	0 285 24	0 285 34
	2000	0 285 05	0 285 15	0 285 25	0 285 35
	2500	0 285 06	0 285 16	0 285 26	0 285 36
	3200	0 285 07	0 285 17	0 285 27	0 285 37
	4000	0 285 08	0 285 18	0 285 28	0 285 38
MP4 protection units	LI	0 288 00			
	LSI	0 288 01			
	LSIg	0 288 02			
Communication option for MP4 protection units					0 288 05
External auxiliary power supply (input 24 V <sub>DC</sub> )					0 288 06
Programmable output option for MP4 protection units					0 288 12
External neutral for DMX <sup>3</sup> 2500 and 4000					0 288 11
<b>DMX<sup>3</sup>-I</b>		<b>TRIP FREE SWITCHES</b>			
In (A)	Fixed version		Draw-out version		
	3P	4P	3P	4P	
<b>Frame 2500</b>					
1250	0 286 83	0 286 93	0 287 83	0 287 93	
1600	0 286 84	0 286 94	0 287 84	0 287 94	
2000	0 286 85	0 286 95	0 287 85	0 287 95	
2500	0 286 86	0 286 96	0 287 86	0 287 96	
<b>Frame 4000</b>					
3200	0 286 87	0 286 97	0 287 87	0 287 97	
4000	0 286 88	0 286 98	0 287 88	0 287 98	
<b>Frame 6300</b>					
6300	0 289 70	0 289 71	0 289 77	0 289 78	