



Technical characteristics see opposite  
Dimensions **p. 240**

Switch-disconnectors and transfer switching equipment equipped with a rotary direct handle. Front operated  
Conform to IEC 60947-3 and IEC 60947-6-1

Pack	Cat.Nos	Switch-disconnectors
		Safety switches for on-load circuit breaking by isolation of the contacts Internal mechanism is independent from the velocity of handle rotation Double break type load switching with self-cleaning contacts by rapid make and break movements Category of use: AC23 A/B (415 V~), Padlockable handle in open position (Ø 6 mm padlock) Cage terminals Accept copper and aluminium cables For 3P+N version, add 1 additional pole (Cat.Nos 4 242 04/05/06/19/20/21) Can be equipped with up to 4 auxiliary contacts (Cat.No 4 242 08), 2 contacts on each side
		<b>Frame 1 - 63 A</b> Width: 1 module per pole
	3P	
1	4 240 00	In 32 A   Number of modules 3
1	4 240 01	40 A   3
1	4 240 02	63 A   3
		<b>Frame 2 - 160 A</b> Width: 1.5 module per pole
1	4 240 03	100 A   4.5
1	4 240 04	125 A   4.5
1	4 240 05	160 A   4.5

Pack	Cat.Nos	Additional poles (neutral) for switch-disconnectors
		To be clipped onto left or right side of a 3-pole switch-disconnectors Maximum 1 additional pole per switch
		<b>For frame 1 switch-disconnectors</b>
	1P	
1	4 242 04	In 32 A   Number of modules 1
1	4 242 05	40 A   1
1	4 242 06	63 A   1
		<b>For frame 2 switch-disconnectors</b>
1	4 242 19	100 A   1.5
1	4 242 20	125 A   1.5
1	4 242 21	160 A   1.5

Pack	Cat.Nos	Transfer switching equipment
		Category of use: AC33 A/B (415 V~) Internal mechanism is independent from the velocity of handle rotation Padlockable handle in open position (Ø 6 mm padlock) Cage terminals Accept copper and aluminium cables Can be equipped with up to 4 auxiliary contacts (Cat.No 4 242 08), 2 contacts on each side
		<b>Frame 1 - 63 A</b> Width: 1 module per pole
		In   Position of the handle   Connection   Number of modules
1	4 241 00	32 A   I - O - II      6   8
1	4 241 01	40 A   I - O - II      6   8
1	4 241 02	63 A   I - O - II      6   8
		<b>Frame 2 - 160 A</b> Width: 1.5 module per pole
1	4 241 03	100 A   I - O - II      9   12
1	4 241 04	125 A   I - O - II      9   12
1	4 241 05	160 A   I - O - II      9   12

Pack	Cat.Nos	Auxiliary contacts (NO+NC)
		For DSX switch-disconnectors and transfer switching equipment 5 A - 230 V~ Can be mounted on both sides of the switches Maximum 4 auxiliaries per switch (2 on each side) Width: 0.5 modules
1	4 242 08	Simultaneous auxiliary Indicates the state of the contacts 