

Isolator switches



7 353 00

Technical characteristics and dimensions p. 256

Pack	Cat.Nos	Isolator switches AC22A
1	7 353 00	2P 250 V~ 50/60Hz
1	7 353 01	2P 20 A
1	7 353 02	2P 32 A
1	7 353 03	2P 40 A
1	7 353 03	2P 63 A
		3P 440 V~ 50/60Hz
1	7 353 10	3P 20 A
1	7 353 11	3P 32 A
1	7 353 12	3P 40 A
1	7 353 13	3P 63 A
		3P + Neutral 440 V~ 50/60Hz
1	7 353 20	4P 20 A
1	7 353 21	4P 32 A
1	7 353 22	4P 40 A
1	7 353 23	4P 63 A

Proximity switching from 16 A to 80 A

Compatible with auxiliary contact



0 221 71

0 221 75

0 227 00

0 222 82

Technical characteristics p. 257
Dimensions p. 258

Safety switch for disconnection and isolation of phases
IP 2X
Double breaking on each phase
Red rotary handle on yellow plate
Immediate display of position
- horizontal: open (O)
- vertical: closed (I)
Equipped with non reversible terminals
Conform to IEC EN 60947-3
UL-cUL (USA and Canada) agreements (except boxes)
IP 65 - IK 07 for boxes

Pack	Cat.Nos	Proximity switching
		Can be equipped with auxiliary contact Cat.No 0 227 00 Padlockable boxes for on-load breaking, isolation and locking in O position Equipment located remotely from a control cabinet Applications: breaking of CMV (controlled mechanical ventilation), motors, fixed or moving machines, air-conditioners
		3P - yellow box
1	0 221 71	16 A
1	0 221 72	20 A
1	0 221 73	25 A
		3P - grey box
1	0 221 74	40 A
1	0 221 75	50 A
1	0 221 76	63 A
1	0 221 77	80 A
		3P + N/O + N/C - yellow box
1	0 221 89	16 A
1	0 221 79	20 A
1	0 221 88	25 A
		4P - neutral on left-hand side - yellow box
1	0 221 81	16 A
1	0 221 82	20 A
1	0 221 83	25 A
		4P - neutral on left-hand side - grey box
1	0 221 84	40 A
1	0 221 85	50 A
1	0 221 86	63 A
1	0 221 87	80 A
		Accessories
		Auxiliary contact N/O + N/C
1	0 227 00	
		Labels Marked "Main switch"
5	0 222 82	Duty label for padlockable faceplate