

# Distribution enclosures XL<sup>3</sup> 6300



0 211 37

Assembly consisting of:  
 - Roof-base Cat.No 0 211 35  
 - Structural uprights Cat.No 0 211 36  
 - Functional uprights Cat.No 0 211 37  
 - Rear panel Cat.No 0 211 41  
 - Support frame for faceplates Cat.No 0 208 55  
 - Lifting rings Cat.No 0 205 82



0 208 00



0 211 40



0 211 39

IP 30 - IK 07

Consist of the combination of a "roof-base" assembly, structural uprights, rear and side panels RAL 7035, plinths RAL 7004  
 Height 2200 mm, usable faceplate height 2000 mm

Pack	Cat.Nos	Enclosures modular metal		
1	0 211 36	<b>Structural uprights</b> Fit onto the "roof-base" assembly Take the side and rear panels Set of 4 uprights		
		<b>"Roof-base" for enclosure</b> Fitted with cable entry plates Take the structural uprights		
		Depth (mm)	Width (mm)	
			external	usable
1	0 211 33	475	1425	1300
1	0 211 34	725	1425	1300
1	0 211 35	975	1425	1300
		<b>Side panels</b> Fixed with screws		
1	0 208 57	Width 475 mm		
1	0 208 58	Width 725 mm		
1	0 208 59	Width 975 mm		
		<b>Rear panel</b> Fixed with screws		
1	0 211 41	Width 1300 mm (supplied in two parts)		
		<b>Finishing panels IP 30</b> 1300 x 2000 mm		
		<b>Plinths that can be placed side by side</b>		
		Height (mm)	Depth (mm)	Width (mm)
1	0 211 30	100	475	1425
1	0 211 31	100	725	1425
1	0 211 32	100	975	1425
		<b>Equipment</b>		
		<b>Functional uprights</b> For fixing mounting equipment (faceplate, rails...) Set of 2 functional uprights		
1	0 211 37			
		<b>Support frame for faceplates</b> Fixed for enclosure width 725 mm or enclosure width 975 mm		
1	0 208 55			
		<b>Isolating supports for busbars 6300 A</b> Supports for 3 bars 200 x 10 mm (per phase)		
1	0 373 12	Fixed support		
1	0 373 13	Additional support Mounted in addition to fixed support Cat.No 0 373 12 to comply with the distances (depending on the Isc)		

Pack	Cat.Nos	Mounting equipment	
		<b>Joining</b>	
1	0 205 86	Screws for structural joining	
1	0 205 88	Set of 2 L-shaped reinforcement plates	
1	0 205 89	Set of 2 flat reinforcement plates	
		<b>Lifting rings</b>	
1	0 205 82	Set of 4 Max. load: 480 kg per ring	
		<b>Fixing modular devices on rail</b>	
		<b>Rail</b>	
		Comprising: an aluminium profile rail and two 2-position fixing brackets Fit onto functional uprights	
1	0 211 42	For fixing on XL <sup>3</sup> 6300 functional uprights 36 modules	
		<b>Metal faceplate for rail equipment</b>	
1	0 208 00	Height 200 mm	
		<b>Fixing devices for DMX<sup>3</sup> 6300</b>	
		<b>Fixing plates</b>	
1	0 211 38	For 1 DMX <sup>3</sup> 6300 3P/4P fixed version	
1	0 211 40	For 1 DMX <sup>3</sup> 6300 3P/4P draw-out version	
		<b>Metal faceplate</b>	
1	0 211 39	For 1 DMX <sup>3</sup> 6300 3P/4P fixed or draw-out version	
		<b>Metal solid faceplates</b>	
1	0 211 44	Height 200 mm, width 1300 mm	
1	0 211 45	Height 400 mm, width 1300 mm	
		<b>Forms of separation equipment</b>	
1	0 211 46	DMX <sup>3</sup> 6300 compartment kit (form 4b)	
1	0 211 47	Partitioning for 6300 A busbars	
1	0 211 49	Kit for horizontal separation (up and down)	

Download XL<sup>3</sup> 4000/6300  
 Workshop specifications on  
[www.expert.legrand.com](http://www.expert.legrand.com)

