


Atlantic, Atlantic stainless steel and Marina cabinets equipment



0 462 28 supplied not assembled



0 367 36



0 362 56
on stand Cat.No 0 364 36
and cross-pieces
Cat.No 0 364 39



0 364 45

Cabinet and equipment selection chart p. 414-415
Technical characteristics p. 437

Pack Cat.Nos Lina 25 sectioned uprights

Pack	Cat.Nos	For cabinets height (mm)	Length (mm)	Section
5	0 361 50 ¹	300	237	
5	0 361 51	400	337	
5	0 361 52	500	437	
5	0 361 53	600	537	
5	0 361 54	700	637	
5	0 361 55	800	737	
5	0 361 56	1000	937	
1	0 361 58	1200	1137	
1	0 361 59 ¹	1400	1337	
10	0 361 92	Upright to be cut Length 3 m - Section L		

Pack	Cat.Nos	For cabinets width (mm)	Crosspiece length (mm)	Section
10	0 367 80	300	243	
10	0 367 81	400	343	
10	0 367 82	500	443	
10	0 367 83	600	543	
10	0 367 84	800	743	
10	0 367 85	1000	943	
10	0 367 86	1200	1143	
10	0 374 02	Rail to be cut, length 2 m EN 60715		
10	0 374 07	Symmetrical depth 15 mm		
10	0 374 04	Symmetrical EN 60175 depth 7.5 mm		
10	0 477 22	depth 7.5 mm with oblongs		
10	0 477 23	depth 15 mm with oblongs		

Pack	Cat.Nos	Support lug for protection copper bar
5	0 367 36	Support lug for protection copper bar For Atlantic enclosures only

Pack	Cat.Nos	For integrating 19" VDI equipment in Atlantic, and Marina cabinets, width 600 or 800 mm and depth 250 mm min.
1	0 462 27	6 U chassis
1	0 462 28	12 U chassis
1	0 462 29	16 U chassis

1: For Atlantic and Atlantic stainless steel only

Pack Cat.Nos Fixing accessories on ground

Pack	Cat.Nos	Stand comprised of 2 feet for fixing cabinets high up
1	0 364 36	Supplied with cabinet fixing screws Hot galvanized steel Conform to EN 50125-3 (railway applications, fixed installations) For Atlantic, Atlantic stainless steel and Marina cabinets
1	0 364 37	For cabinets height 400 to 800 mm
1	0 364 39	For cabinets height 1000 to 1200 mm Anti-tipping cross-pieces Option of fitting casters Cat.No 0 464 83 (p. 423)
1	0 364 46	Fixing accessories vertical / horizontal on pole For Atlantic, Atlantic stainless steel, and Marina enclosures and P17 combined units (p. 536) Features of the pole kit: - box / pole spacing = 30 mm - clamping the strip with tool Cat.No 0 364 45 Load capacity: 300 kg Composed of: - 2 hot-dip galvanized steel crosspieces - 2 stainless steel strips length: 1200 mm, with integrated clip - screws
1	0 364 47	For enclosures width 300 mm
1	0 364 48	For enclosures width 400 mm
1	0 364 49	For enclosures width 500 mm For enclosures width 600 mm

Pack	Cat.Nos	Allows to stretch and cut the steel strips
1	0 364 45	Supplied in a briefcase