

## Marina cabinets fixing accessories

### installation principle



Marina cabinet fixed on a vertical pole with kit Cat.No 0 364 48 (p. 431)



Atlantic cabinet fixed on a horizontal pole with kit Cat.No 0 364 48 (p. 431)



0 364 45 (p. 431)

### Horizontal or vertical fixing on pole

Height x Width (mm)	Atlantic		Marina	
300 x 300	0 364 46	0 364 46	-	-
400 x 300	0 364 46	0 364 47	0 364 46	0 364 47
300 x 400	0 364 47	0 364 46	-	-
400 x 400	0 364 47	0 364 47	-	-
500 x 400	0 364 47	0 364 48	0 364 47	0 364 48
600 x 400	0 364 47	0 364 49	0 364 47	0 364 49
500 x 500	0 364 48	0 364 48	-	-
700 x 500	0 364 48	-	0 364 48	-
400 x 600	0 364 49	0 364 47	-	-
600 x 600	0 364 49	0 364 49	-	-
800 x 600	0 364 49	-	0 364 49	-
1000 x 600	0 364 49	-	-	-
600 x 800	-	0 364 49	-	-
600 x 1000	-	0 364 49	-	-

## Marina enclosures

### polyester - IP 66 - IK 10



0 362 85



0 362 86 with plinth Cat.No 0 362 96  
internal door Cat.No 0 363 67  
and roof Cat.No 0 362 97



### Technical characteristics p. 426 to 428

IP 66 acc. to IEC EN 60529  
LCIE n° 60059283-560528  
IK 10 acc. to EN 62262 (EN 50102)  
Class II (Used to create totally isolated assemblies acc. to EN 60439-1)  
Fiberglass reinforced polyester  
Self-extinguishing 960°C acc. to IEC EN 60695-2-11  
Adapted to corrosive environment  
Supplied with fixing kit for plain plates or sectioned uprights  
Depth adjustment of equipment  
Equipped with low cable entries plate  
Reversible door with strand-holder  
3 point closing with handle fitted with 1/2 locking latch 2433 A (other key code, please consult us)  
Stainless steel hinges and hinges axis

Pack	Cat.Nos	Enclosures RAL 7035	Corresponding metal enclosures (mm)
		External dimensions (mm)	Height x Width x Depth
		Height x Width x Depth	Height x Width x Depth
1	0 362 85	1460 x 800 x 463	1400 x 800 x 400
1	0 362 86	1660 x 800 x 463	1600 x 800 x 400
1	0 362 87	1860 x 800 x 463	1800 x 800 x 400
		<b>Plinth RAL 7035</b>	
		Height 170 mm	
		Front and rear trap door	
1	0 362 96	Possibility to overlap 2 plinths	
		For enclosure width 800 x depth 400 mm	
		<b>Roof RAL 7035</b>	
1	0 362 97	For enclosure width 800 x depth 400 mm	



Altis automation enclosures for specific applications,  
**Please, consult us**

