


Viking™ 3 terminal blocks with spring connection

for copper cables (continued)



Technical characteristics **p. 467**
 Dimensions **p. 468**

Screwless connection system, stainless steel spring type
 Used to make the electrical connection between 2 rigid copper wires, or flexible copper wires with or without ferrules (p. 472)
 Direct tool-free insertion of a rigid wire or flexible wire with ferrule, up to 6 mm pitch
 2 areas for automatic insertion bridging combs (upper level only for 2-level blocks)
 For rails depth 15 mm, EN 60715 depth 7.5 mm and 15 mm

Pack	Cat.Nos	Disconnect terminal blocks 1 connection - 2 wires				
		Opening by means of blade type lever, handle lever or mini lever (with tool)				
		Open (to be equipped)				
		Can take blade type levers Cat.Nos 0 375 15/16/17/18 or in ELV installations a blade-type automotive fuse or a miniature circuit-breaker				
			Nominal cross-section (mm²)	Rigid wire (mm²)	Capacity Flexible wire (mm²)	Pitch (mm)
20	0 372 80	Colour Grey	2.5	0.5 to 2.5	0.5 to 2.5	6
20	0 372 81	Grey	2.5	0.5 to 2.5	0.5 to 2.5	6
20	0 372 82	Grey/blue	2.5	0.5 to 2.5	0.5 to 2.5	6
20	0 372 83	Grey	2.5	0.5 to 2.5	0.5 to 2.5	6
20	0 372 84	Grey	2.5	0.5 to 2.5	0.5 to 2.5	6
20	0 372 85	Orange	2.5	0.5 to 2.5	0.5 to 2.5	6
20	0 372 86	Orange	2.5	0.5 to 2.5	0.5 to 2.5	6

Pack	Cat.Nos	Function blocks				
		1 connection - 4 wires - 2 entries/2 outlets - diode carrier				
60	0 372 54	Colour Grey	Nominal cross-section (mm²) 4	Rigid wire (mm²) 0.5 to 6	Capacity Flexible wire (mm²) 0.5 to 4	Pitch (mm) 5
60	0 372 55	Grey	4	0.5 to 6	0.5 to 4	5
60	0 372 56	Grey	4	0.5 to 6	0.5 to 4	5

Blade type levers, joining rods and blown fuse indicators **p. 463**

Accessories **p. 462**

Starfix ferrules and crimping tools **p. 472**

