

# Arteor™

## wireless power chargers



0 776 40L supplied with sticker

0 776 99L

Wireless power chargers for fast charging of a smartphone with a Qi receiver  
 Power supply standby mode consumption < 0.07 %  
 Conform to the Qi WPC standard (Wireless Power Consortium): certified for professional Qi 1.2.3 projects  
 Conform to EN 62479 standard (EMF emissions)  
 Conform to ICNIRP specifications (health protection)  
 Do not interfere with other wireless signals (Zigbee, TNT, GSM, 4G, etc)

Pack	Cat.Nos	Qi wireless charger - for integration into furniture
1	0 776 40L	<p>Specially designed for mounting horizontally on furniture                      For meeting rooms, offices, public areas, etc                      80 mm drilling diameter, Aluminium colour                      Extra-slim with thickness &lt; 1.5 mm                      Supplied with identification sticker diameter 85/110 mm, 2.5 m cord, fixing base and cable ties                      110-240 V universal power supply                      Plugs conforming to European, BS, US, Australian/ Chinese standards                      To be installed using a hole saw diameter 80 mm (Cat.No 0 885 08 p. 1167)                      15 W - IP 44 / IK 08 charger</p>

1	0 776 99L	<p><b>Flush-mounted wireless charger - for public areas</b></p> <p>10 W wireless charger                      Specially designed for public buildings, passageways or transit areas, swimming pools, etc.                      IK 08 - IP 66 - Class II SELV                      Comes with 2 induction antennae for fast smartphone charging                      Recognition area: 50 x 80 mm                      Plate at an angle of 10° with non-slip coating to hold the terminal safely in place during charging                      Screws onto flush-mounting box with 60 mm fixing centres, min. depth 40 mm, French, German or British standard                      Can also be fixed in at 4 points                      Can be mounted on rectangular boxes and outdoors                      110/230 VA Phase + Neutral power supply                      Mechanism supplied with cover plate, attached with 2 Torx screws at the side</p> <ul style="list-style-type: none"> <li>● Aluminium colour</li> </ul> <p>Dimensions: 141 x 95 x 51 mm                      2 x 2.5 mm<sup>2</sup> terminals</p>
---	-----------	---

# Arteor™

## wireless power chargers

### Wireless power charging

#### A Legrand innovation for easy charging


Using wireless energy transfer  
 No need for cords and connectors

#### An open international standard:

Wireless Power Consortium: 750 members, ensuring interoperability with induction-compatible phones  
 Qi: global standard adopted by vehicle manufacturers and cafés/hotels/restaurants  
 Products certified for professional Qi 1.2.3 projects

### Ergonomically designed to suit different environments


#### Horizontal charging on furniture



Insertion in an 80 mm diameter cut-out / Fixed into furniture  
 External power supply with 2.5 m cord

#### Vertical charging on a wall in public areas (semi-flush-mounted)

Ideal for indoor or outdoor locations



Excellent resistance to impacts (IK 08) and adverse weather conditions (IP 66)  
 Can be fixed directly on the flush-mounting box or for extra strength drilled with anchor bolts