

Arteor™ with Netatmo - International

connected light switches (continued)

Step 2: Connected products



Home + Control



5 743 40



5 743 33



0 648 99



Support frame and plate selection charts **p. 594 to 603**

Used to create your connected installation, require prior installation of a gateway pack for connected installation Zigbee Certified Product

Pack	Cat.Nos	Connected light switches (continued)
		Switch with neutral, 150 W LED, with dimmer option, wired Mechanisms supplied with cover plates, to be equipped with support frames (p. 614) and plates (p. 594-603) For local or remote ON/OFF or dimming control of lighting Can be controlled by one or several wireless light switches and/or mechanical push-buttons without neon Dimmer mode and locator/ indicator functions can be activated from the Home + Control App. Compatible with all loads: - Dimmable LEDs and CFL lamps: 150 W LED - Incandescent and halogen lamps: 150 W - ELV halogen and CFL lamps with separate ballast: 150 VA Memory level function Can be installed in place of an existing switch in a flush-mounting box depth 35 mm
1	5 743 40	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 743 42	
1	5 743 43	
1	5 743 41	
		2 modules
1	5 743 30	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 743 32	
1	5 743 33	
1	5 743 31	

Connected micromodule switches with neutral

1	5 742 43	Used to connect lights with a ceiling box installation Can be controlled by one or more wireless light switches and/or mechanical push-buttons ON/OFF switch 100 W LED, wired Compatible with all loads: - LEDs and CFL lamps: 100 W LED - Incandescent and halogen lamps: 300 W - ELV halogen and CFL lamps with separate ballast: 250 VA
1	0 648 99	Switch with dimmer option, 150 W LED, wired For local or remote ON/OFF / dimming control of lighting Dimmer mode can be activated from the Home + Control App. Memory level function Compatible with all loads: - dimmable LEDs and CFL lamps: 150 W LED - Incandescent and halogen lamps: 150 W - ELV halogen and CFL lamps with separate ballast: 150 VA

Arteor™ with Netatmo - International

connected socket outlets

Step 2: Connected products



Home + Control



5 742 00



5 742 00 + 5 721 04
+ plate 5 752 10



0 648 89



Support frame and plate selection charts **p. 594 to 603**

Used to complete your connected installation, require prior installation of a gateway pack for connected installation Zigbee Certified Product

Pack	Cat.Nos	Connected socket outlet module - 16 A - 230 V~ - 3680 W, 1 module
		Mechanisms supplied with cover plates, to be equipped with support frames (p. 614) and plates (p. 594-603) Allows to create a connected socket outlet for integration into the connected installation To be wired to a traditional socket outlet Connected socket outlets can be controlled by one or several wireless light switches Remote control via the Home + Control App. Compatible with any electrical appliance or large household appliance Connected socket outlets allow to - remotely control electrical appliances - measure instantaneous power - monitor daily and monthly consumption - send notifications in case of abnormal use (overconsumption etc.) Can be installed in place of an existing socket outlet in a flush-mounting box min. depth 40 mm Indicator LED function can be activated from the Home + Control App.
1	5 742 00	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 742 28	
1	5 742 37	
1	5 742 19	
		Connected mobile socket outlets
		Conform to IEC 60884-2-5 and IEC 60669-2-5 To be plugged directly into an existing socket outlet For control of lights, electrical appliances and large household appliances Can be controlled by one or several wireless light switches - ON/OFF indicator LED function Connected mobile socket outlets allow to - remotely control electrical appliances - measure instantaneous power - monitor daily and monthly consumption - send notifications in case of abnormal use (overconsumption etc.) Indicator LED function can be activated from the Home + Control App.
1	0 648 89	13 A British standard connected mobile socket outlet - 3000 W ● Magnesium
1	5 742 54	16 A German standard connected mobile socket outlet - 3680 W ● Magnesium