

## Bells for industrial and alarm use

## Electromechanical and electronic siren



Pack	Cat.Nos	<b>Class I</b>			
		Double insulated Polyester corrosion resistant finish 200 hours maxi. continuous rating			
		<b>IP 40 - IK 08 - 50/60 Hz - Alternating current version</b>			
		Ø100 mm gong			
1	RAL 7037 Grey 0 413 49	Voltage ~ 230 V	Consumption (mA) 50	Average acoustic output at 1 m (dB) 95	Weight (kg) 0.8
		<b>IP 44 - IK 10</b>			
		Ø150 mm gong			
1	0 414 16	24V	360	98	1
1	0 414 18	110/130 V	90	98	1
1	0 414 19	230 V	50	98	1
		<b>IP 44 - IK 10</b>			
		Ø250 mm gong			
1	0 414 39	230 V	70	98	2.1



Technical characteristics and chart of sounds p. 553

Pack	Cat.Nos	<b>Industrial warning devices 110 dB IP 20 - IK 08</b>					
		Frequency 350/400 Hz, continuous sound Operates intermittently: 1 min on / 10 min off					
1	0 415 20	24 V~ and = power supply		Consumption in mA 820			
1	0 415 23	230 V~ power supply		120			
		<b>Electromechanical sirens IP 30 - IK 05</b>					
		Supplied with screws for semi-flush mounting					
		<b>D.C. current</b>					
		Voltage =	Power (W)	Consumption (mA)	Average acoustic output at 1 m (dB)	Weight (kg)	Max. continuous rating (hr)
1	0 415 32	12 V	11	889	98	0.2	200
1	0 415 33	24 V	12	516	100	0.2	200
		<b>A.C. current - 50/60 Hz</b>					
		Voltage ~	Power (W)	Consumption (mA)	Average acoustic output at 1 m (dB)	Weight (kg)	Max. continuous rating (hr)
1	0 415 36	24 V	12.5	531	100	0.2	200
1	0 415 38	110 V	70	400	105	0.35	100
1	0 415 39	230 V	57	250	105	0.35	100
		<b>Multi-sound electronic siren</b>					
		To be equipped with base for LED beacons and multi-sound electronic sirens Cat.Nos 0 413 81/82/83 (p. 552) 64 electronic sounds possible, 2 channels Configuration by microswitches Adjustable sound level from 54 to 102 dB (1m) Dimensions: Ø92 mm x 60 mm Power supply from 12 V AC/DC to 230 V AC depending on the installed base					
1	0 413 98	IP 65 - IK 08					