








### Loads that can be driven (110 V $\sim$ - max. 250 V $\sim$ 50/60 Hz)

Cat.Nos									
		Energy saving incandescence and halogen lamps	LED lamps	Linear fluorescent lamps	Compact fluorescent lamps	Electronic transformers	Ferromagnetic transformers	Reducer motors for shutters	
BT-BMSW1005	250 V $\sim$	-	-	4.3 A 10 x 2 x 36 W	5 A 1150 VA	16 A 3680 W	16 A 3680 W	-	
	110 V $\sim$	-	-	4.3 A 5 x (2 x 36 W)	5 A 550 VA	16 A 1760 W	16 A 1760 W	-	
BT-BMSW1003	250 V $\sim$	-	-	10x(2x36 W) 4.3 A	1150 W 5 A	16 A 3680 W	16 A 3680 W	-	
	110 V $\sim$	-	-	10x(2x36 W) 4.3 A	550 W 5 A	16 A 1760 W	16 A 1760 W	-	
BT-F411U2	250 V $\sim$	-	-	4 A 920 W	500 W	920 W	4 A Cos $\varphi$ 0.5 920 VA	2 A 460 W	
	110 V $\sim$	-	-	4A 440W	250W	440W	4A Cos $\varphi$ 0.5 440 VA	2A 250W	
BT-3476	250 V $\sim$	2 A 460 W	40 W MAX 1 LAMP	-	40 W MAX 1 LAMP	-	2A Cos $\varphi$ 0.5 460 VA	-	
	110 V $\sim$	2 A 220 W	20 W MAX 1 LAMP	-	20 W MAX 1 LAMP	-	2 A Cos $\varphi$ 0.5 220 VA	-	
BT-F401	250 V $\sim$	-	-	-	-	-	-	2 A 250 W	
	110 V $\sim$	-	-	-	-	-	-	2 A 220 W	
BT-F411/1NC	250 V $\sim$	10 A 2300 W	500 W MAX 10 LAMPS	4 A 920 W	500 W MAX 10 LAMPS	4 A 920 W	4 A Cos $\varphi$ 0.5 920 VA	-	
	110 V $\sim$	10 A 2300 W	220 W MAX 10 LAMPS	4 A 440 W	220 W MAX 10 LAMPS	4 A 440 W	4 A Cos $\varphi$ 0.5 440 VA	-	
BT-F411/4	250 V $\sim$	2 A 460 W	70 W MAX 2 LAMPS	0.3 A 70 W	70 W MAX 2 LAMPS	0.3 A 70 W	2 A Cos $\varphi$ 0.5 460 VA	2 A 460 W	
	110 V $\sim$	2 A 220 W	35 W MAX 2 LAMPS	0.3 A 35 W	35 W MAX 2 LAMPS	0.3 A 35 W	2 A Cos $\varphi$ 0.5 220 VA	2 A 220 W	
BT-BMD11002	250 V $\sim$	Dimmer for ballast 4x4.3 A outputs - 4x1000VA							
	110 V $\sim$	Dimmer for ballast 4x4.3 A outputs - 4x500 VA							
BT-F418U2	250 V $\sim$	2x300 W	2x300 VA	-	2x300 VA	2x300 VA	2x300 VA	-	
	110 V $\sim$	2x150 W	2x150 VA	-	2x150 VA	2x150 VA	2x150 VA	-	
BT-F416U1	250 V $\sim$	4.3 A 40-1000 W	-	-	-	4.3 A 40-1000 W	4.3 A 40-1000 W	-	
	110 V $\sim$	4.3 A 500 W	-	-	-	4.3 A 500 W	4.3 A 500 W	-	
BT-F413N	250 V $\sim$	-	-	2 A max 10 ballast 460 W	-	-	-	-	
	110 V $\sim$	-	-	2 A max 10 ballast 220 W	-	-	-	-	
0 675 61	To use with connected neutral	250 V $\sim$	1380 W 6 A	250 W 1 A	460 W 2 A	-	-	460 VA 2 A Cos $\varphi$ 0.5	460 W 2 A
		110 V $\sim$	660 W 6 A	110 W 1 A	220 W 2 A	-	-	220 VA 2 A Cos $\varphi$ 0.5	250 W 2 A
	To use without neutral or 10 maxi lamps. For good lighting comfort, we recommend the use of lamps of the same type and from the same supplier	250 V $\sim$	460 W 2 A	-	-	-	-	460 VA 2 A Cos $\varphi$ 0.5	460 W 2 A
		110 V $\sim$	220 W 2 A	-	-	-	-	220 VA 2 A Cos $\varphi$ 0.5	250 W 2 A
0 675 57	250 V $\sim$	-	-	-	-	-	-	1x460 W	
	110 V $\sim$	-	-	-	-	-	-	1x230 W	