

# Galion™

double pole switches 45 A, cooker units, dimmers, active power bleeder and fan controls



2 824 27-C



2 824 25



2 824 19-C1



2 824 90

Conform to IEC 60669-1 standard  
 Material: Polycarbonate front cover plates  
 Dimensions: 86 x 88 mm  
 Supplied with 2 screws M 3.5 for BS boxes. Supplied complete with plate

Pack	Cat.Nos	Double pole switches 45 A - 250 V~
		With red LED power indicator
8	2 824 26	<b>1-gang 1-way</b> <ul style="list-style-type: none"> <li>○ White</li> <li>● Matt Black</li> <li>● Rose Gold</li> <li>● Champagne</li> <li>● Dark Silver</li> </ul>
8	2 824 26-C	
8	2 824 26-C1	
8	2 824 26-C2	
8	2 824 26-C3	
8	2 824 27	<b>1-gang 1-way with red rocker</b> <ul style="list-style-type: none"> <li>○ White</li> <li>● Matt Black</li> <li>● Rose Gold</li> <li>● Champagne</li> <li>● Dark Silver</li> </ul>
8	2 824 27-C	
8	2 824 27-C1	
8	2 824 27-C2	
8	2 824 27-C3	
8	2 824 28	<b>1-gang 1-way with "cooker" marking - with red rocker</b> <ul style="list-style-type: none"> <li>○ White</li> <li>● Matt Black</li> <li>● Rose Gold</li> <li>● Champagne</li> <li>● Dark Silver</li> </ul>
8	2 824 28-C	
8	2 824 28-C1	
8	2 824 28-C2	
8	2 824 28-C3	
8	2 824 29	<b>2-gang (vertical) 1-way with red rocker</b> Dim.: 86 x 146 mm <ul style="list-style-type: none"> <li>○ White</li> <li>● Matt Black</li> <li>● Rose Gold</li> <li>● Champagne</li> <li>● Dark Silver</li> </ul>
8	2 824 29-C	
8	2 824 29-C1	
8	2 824 29-C2	
8	2 824 29-C3	

Pack	Cat.Nos	Cooker units - 250 V~
		Conform to IEC 60884-1 and IEC 60669-1 45 A double pole switch + 13 A British Standard switched socket and amber LED power indicators Dim.: 146 x 88 mm
5	2 824 25	<ul style="list-style-type: none"> <li>○ White</li> <li>● Matt Black</li> <li>● Rose Gold</li> <li>● Champagne</li> <li>● Dark Silver</li> </ul>
5	2 824 25-C	
5	2 824 25-C1	
5	2 824 25-C2	
5	2 824 25-C3	

Pack	Cat.Nos	Dimmers
		100-240 V~, 50/60 Hz
		<b>Rotary dimmers without neutral 40-500 W</b> For incandescent and halogen lamps 230 V~
5	2 824 20	<ul style="list-style-type: none"> <li>○ White</li> <li>● Matt Black</li> <li>● Rose Gold</li> <li>● Champagne</li> <li>● Dark Silver</li> </ul>
5	2 824 20-C	
5	2 824 20-C1	
5	2 824 20-C2	
5	2 824 20-C3	
		<b>Rotary dimmers without neutral - 300 W RLC + LED</b> Conform to IEC 60669-2-1 For all types of lamps: - dimmable LEDs and CFL lamps: 5 to 75 W LED - halogen with ferromagnetic or electronic transformer: 5 to 300 VA - fluorescent tube - ballast: 5 to 300 VA - halogen and incandescent 230 V~: 5 to 300 W
5	2 824 19	<ul style="list-style-type: none"> <li>○ White</li> <li>● Matt Black</li> <li>● Rose Gold</li> <li>● Champagne</li> <li>● Dark Silver</li> </ul>
5	2 824 19-C	
5	2 824 19-C1	
5	2 824 19-C2	
5	2 824 19-C3	

Pack	Cat.Nos	Active Power Bleeder
1	0 401 49	Makes 2-wire electronic lighting control units without neutral compatible with all commercially-available loads (LED, compact fluorescent, ELV halogen with ferromagnetic or electronic ballast, 230 V halogen, fluorescent tube, incandescent) Consumption: 0.4 W

Pack	Cat.Nos	Stepless fan controls
		40-400 VA, 230 V~, 50/60 Hz
5	2 824 90	<ul style="list-style-type: none"> <li>○ White</li> <li>● Matt Black</li> <li>● Rose Gold</li> <li>● Champagne</li> <li>● Dark Silver</li> </ul>
5	2 824 90-C	
5	2 824 90-C1	
5	2 824 90-C2	
5	2 824 90-C3	