

Arteor™ with Netatmo - International

connected gateway pack

Must be ordered for any connected installation

Step 1: Gateway pack for a connected home



Home + Control



5 742 09

Support frame and plate selection charts p. 594 to 603

Used to create the radio network and the Wi-Fi connection of the connected installation
Enables remote control of your home (lighting, curtains/roller blinds, temperature and electrical appliances) using a smartphone via the Home + Control App. and/or voice control with a voice assistant
Must be ordered to start any connected installation
To be completed by adding individual connected products
2.4 GHz Wi-Fi connection required

Pack	Cat.Nos	Connected gateway pack
1	5 742 09	<p>Used to create the radio network and the Wi-Fi connection Composition: - 1 flush-mounted Zigbee/Wi-Fi gateway Mechanisms supplied with cover plates, to be equipped with support frames (p. 614) and plates (p. 594-603) Allows the connection of the installation to the Wi-Fi network and enables control through the Home + Control App. and voice assistants (Google Assistant, Amazon Alexa, Apple Siri)⁽¹⁾ Can be installed in place of an existing product Suitable for flush-mounting box min. depth 35mm - 1 Home/Away wireless master switch with preset life scenes Supplied with cover plate and multi-standard support frame (with removable fins) To be equipped with 2-module plates Used to create the radio network and to control life scenes Life scenes can be customised in the Home + Control App. Supplied with CR2032 3 V long-life battery for power supply and removable stickers for fixing the control unit on any substrate LED function for low battery indication</p> <p> </p> <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 742 27	
1	5 742 36	
1	5 742 18	

1: Availability of voice assistants to be checked in your country

Arteor™ with Netatmo - International

connected light switches

Step 2: Connected products



Home + Control



5 742 01



5 742 12A

Support frame and plate selection charts p. 594 to 603

Used to create your connected installation, require prior installation of a gateway pack for connected installation
Zigbee Certified Product

Pack	Cat.Nos	Connected light switches
		<p>Mechanisms supplied with cover plates, to be equipped with support frames (p. 614) and plates (p. 594-603) Can be installed in place of an existing switch in a flush-mounting box depth 35 mm</p> <p>Switch with neutral 100 W LED, wired, 1 module For local or remote control of lighting Can be controlled by one or several wireless light switches and/or mechanical 2-way switches Compatible with all loads : - LEDs and CFL lamps: 100 W LED - Incandescent and halogen lamps: 500 W - ELV halogen and CFL lamps with separate ballast: 250 VA Locator and indicator functions can be activated from the Home + Control App.</p> <p> </p> <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 742 01	
1	5 742 20	
1	5 742 29	
1	5 742 11	
		<p>Switch without neutral, 125 W LED, with dimmer option, wired, 2 modules For local or remote ON/OFF or dimming control of lighting Can be controlled by one or several wireless light switches and/or mechanical push-buttons Dimmer mode and locator and indicator functions can be activated from the Home + Control App. Compatible with all loads: - Dimmable LEDs and CFL lamps: 125 W LED - Incandescent and halogen lamps: 125 W - ELV halogen and CFL lamps with separate ballast: 125 VA Supplied with a bleeder Memory level function</p> <p> </p> <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 742 02A	
1	5 742 21A	
1	5 742 30A	
1	5 742 12A	

Legrand's Home + Control App. available on Google Play and the App Store



Products to be submitted to local tests to ensure a perfect functioning
Please contact your local agency