

# Mallia™ Senses

## single pole switches (continued)



2 810 10BA



2 810 12CH



2 810 15DS







2 810 69MW






Conform to BS EN 60669-1

Compact mechanism for greater wiring space

Dimensions: 86 x 86 mm

Supplied with 2 screws M 3.5 for BS boxes. Supplied as complete product with protective film

Pack	Cat.Nos	Single pole illuminated switches 16 AX - 250 V~
		Transparent lens To be equipped with warm white or red LED according to the need: indicator or locator (p. 704) The LED is not supplied
5	2 810 10BA	<b>1-gang 1-way switch</b>  <ul style="list-style-type: none"> <li>● Brushed Aluminium</li> <li>● Brushed Black</li> <li>● Champagne</li> <li>● Dark Bronze</li> <li>● Dark Silver</li> <li>● Matt Black</li> <li>○ Matt White</li> </ul>
5	2 810 10BB	
5	2 810 10CH	
5	2 810 10DB	
5	2 810 10DS	
5	2 810 10MB	
10	2 810 10MW	
5	2 810 11BA	<b>1-gang 2-way switch</b>  <ul style="list-style-type: none"> <li>● Brushed Aluminium</li> <li>● Brushed Black</li> <li>● Champagne</li> <li>● Dark Bronze</li> <li>● Dark Silver</li> <li>● Matt Black</li> <li>○ Matt White</li> </ul>
5	2 810 11BB	
5	2 810 11CH	
5	2 810 11DB	
5	2 810 11DS	
5	2 810 11MB	
10	2 810 11MW	
5	2 810 09BA	<b>1-gang intermediate switch</b>  <ul style="list-style-type: none"> <li>● Brushed Aluminium</li> <li>● Brushed Black</li> <li>● Champagne</li> <li>● Dark Bronze</li> <li>● Dark Silver</li> <li>● Matt Black</li> <li>○ Matt White</li> </ul>
5	2 810 09BB	
5	2 810 09CH	
5	2 810 09DB	
5	2 810 09DS	
5	2 810 09MB	
5	2 810 09MW	
5	2 810 12BA	<b>2-gang 1-way switch</b>  <ul style="list-style-type: none"> <li>● Brushed Aluminium</li> <li>● Brushed Black</li> <li>● Champagne</li> <li>● Dark Bronze</li> <li>● Dark Silver</li> <li>● Matt Black</li> <li>○ Matt White</li> </ul>
5	2 810 12BB	
5	2 810 12CH	
5	2 810 12DB	
5	2 810 12DS	
5	2 810 12MB	
10	2 810 12MW	
5	2 810 13BA	<b>2-gang 2-way switch</b>  <ul style="list-style-type: none"> <li>● Brushed Aluminium</li> <li>● Brushed Black</li> <li>● Champagne</li> <li>● Dark Bronze</li> <li>● Dark Silver</li> <li>● Matt Black</li> <li>○ Matt White</li> </ul>
5	2 810 13BB	
5	2 810 13CH	
5	2 810 13DB	
5	2 810 13DS	
5	2 810 13MB	
10	2 810 13MW	

Pack	Cat.Nos	Single pole illuminated switches 16 AX - 250 V~ (continued)
5	2 810 14BA	<b>3-gang 1-way switch</b>  <ul style="list-style-type: none"> <li>● Brushed Aluminium</li> <li>● Brushed Black</li> <li>● Champagne</li> <li>● Dark Bronze</li> <li>● Dark Silver</li> <li>● Matt Black</li> <li>○ Matt White</li> </ul>
5	2 810 14BB	
5	2 810 14CH	
5	2 810 14DB	
5	2 810 14DS	
5	2 810 14MB	
10	2 810 14MW	
5	2 810 15BA	<b>3-gang 2-way switch</b>  <ul style="list-style-type: none"> <li>● Brushed Aluminium</li> <li>● Brushed Black</li> <li>● Champagne</li> <li>● Dark Bronze</li> <li>● Dark Silver</li> <li>● Matt Black</li> <li>○ Matt White</li> </ul>
5	2 810 15BB	
5	2 810 15CH	
5	2 810 15DB	
5	2 810 15DS	
5	2 810 15MB	
10	2 810 15MW	
5	2 810 50BA	<b>Single pole switches 20 AX - 250 V~</b> <b>1-gang 1-way switch</b>  <ul style="list-style-type: none"> <li>● Brushed Aluminium</li> <li>● Brushed Black</li> <li>● Champagne</li> <li>● Dark Bronze</li> <li>● Dark Silver</li> <li>● Matt Black</li> <li>○ Matt White</li> </ul>
5	2 810 50BB	
5	2 810 50CH	
5	2 810 50DB	
5	2 810 50DS	
5	2 810 50MB	
10	2 810 50MW	
5	2 810 51BA	<b>1-gang 2-way switch</b>  <ul style="list-style-type: none"> <li>● Brushed Aluminium</li> <li>● Brushed Black</li> <li>● Champagne</li> <li>● Dark Bronze</li> <li>● Dark Silver</li> <li>● Matt Black</li> <li>○ Matt White</li> </ul>
5	2 810 51BB	
5	2 810 51CH	
5	2 810 51DB	
5	2 810 51DS	
5	2 810 51MB	
10	2 810 51MW	
5	2 810 69BA	<b>1-gang intermediate switch</b>  <ul style="list-style-type: none"> <li>● Brushed Aluminium</li> <li>● Brushed Black</li> <li>● Champagne</li> <li>● Dark Bronze</li> <li>● Dark Silver</li> <li>● Matt Black</li> <li>○ Matt White</li> </ul>
5	2 810 69BB	
5	2 810 69CH	
5	2 810 69DB	
5	2 810 69DS	
5	2 810 69MB	
5	2 810 69MW	