



7 300 00



7 300 06

Front plates: white thermoset. Terminal screws captive and backed off ready for cabling - large angled terminal entries
Compact mechanism for maximised wiring space. Supplied with faceplate screw caps

Pack	Cat.Nos	Single pole plate switches 10 AX - 250 V~
		Conform to BS EN 60669-1 For flush-mounting, back box can be min. 16 mm deep ASTA licence
		Optional red LED "power on" indicator and green LED "locator" upgrade packs available
		Nominal plate dimensions: 86 x 86 mm
10	7 300 00	1-gang 1-way
10	7 300 01	1-gang 2-way
10	7 300 05	1-gang intermediate
10	7 300 24	2-gang 1-way
10	7 300 02	2-gang 2-way
10	7 301 24	3-gang 1-way
10	7 300 03	3-gang 2-way
		Nominal plate dimensions: 86 x 146 mm
5	7 300 04	4-gang 2-way
5	7 300 06	6-gang 2-way
Pack	Cat.Nos	Single pole plate switches 20 AX - 250 V~
		Conform to BS EN 60669-1 For flush-mounting, back box to be min. 16 mm deep Nominal plate dimensions: 86 x 86 mm Optional red LED "power on" indicator and green LED "locator" upgrade packs available
10	7 301 30	1-gang 1-way
10	7 301 31	1-gang 2-way
10	7 301 34	2-gang 1-way
10	7 301 32	2-gang 2-way
10	7 301 35	3-gang 1-way
10	7 301 33	3-gang 2-way

Pack	Cat.Nos	Single pole push switches 10 A - 250 V~
		Conform to BS EN 60669-1 For flush-mounting, back box to be min. 16 mm deep ASTA licence
		Nominal plate dimensions: 86 x 86 mm
5	7 300 07	1-gang 2-way push switch
5	7 300 11	1-gang 2-way push switch marked "PRESS"
5	7 301 07	1-gang 2-way push switch with bell symbol
Pack	Cat.Nos	Single pole key switch 10 AX - 250 V~
		Conform to BS EN 60669-1: 2000 Key supplied. For flush-mounting, back box to be min. 16 mm deep. Nominal plate dimensions: 86 x 86 mm
10	7 300 08	1-gang 2-way
Pack	Cat.Nos	3 pole fan switch 10 A - 250 V~
		Conform to BS EN 60669-1: 2000 With integrated padlockable safety block in OFF position. Flush-mounting back box: min 25 mm deep Nominal plate dimensions: 86 x 86 mm
10	7 300 09	3 pole fan switch

Surface mounting boxes,
p. 721



Green locator LED pack or red power indicator pack
p. 721

