

Synergy™

dimmers



7 311 51



7 301 56

Front plates: white thermoset
Terminal screws captive and backed off ready for cabling - large angled terminal entries
Compact mechanism for maximised wiring space
Supplied with faceplate screw caps

Pack	Cat.Nos	
1	7 311 51	<p>Push ON/OFF rotary universal dimmer 5 W/300 W 100 - 240 V~ - 50/60 Hz</p> <p>Conform to IEC 60669-2-1 For flush-mounting back box to be min. 40 mm deep Equipped with overvoltage and short-circuit protection Screw terminals. For all types of lamps: - dimmable LEDs and CFL lamps: 5 to 75 W LED - halogen with ferromagnetic or electronic transformer: 5 to 300 VA - fluorescent tube - ballast: 5 to 300 VA - halogen and incandescent 230 V: 5 to 300 W When switched on, gradually (2 seconds) lights up at the level set before last switch-off Nominal plate dimensions: 86 x 86 mm</p> <p>1-gang Can be associated with an active power bleeder (p. 727)</p>
1	7 301 56	<p>Push ON/OFF rotary dimmers 400 W 100 - 240 V~ - 50/60 Hz</p> <p>Conform to BS EN 60669-1 For flush-mounting, back box to be min. 25 mm deep Nominal plate dimensions: 86 x 86 mm</p> <p>1-gang 2-way</p>
1	7 301 57	<p>2-gang 2-way</p>
1	7 300 49	<p>Nominal plate dimensions: 86 x 146 mm</p> <p>4-gang 2-way</p>
1	7 301 50	<p>Push ON/OFF rotary dimmer 1000 W 100 - 240 V/50-60 Hz</p> <p>Conform to BS EN 60669-1 - For flush-mounting back box to be min. 40 mm deep - 60-1000 W (230 V) - 60-500 W(127 V) for incandescent and halogen lamps 60-600 VA (230 V) - 60-300 VA (127 V) for halogen lamps with electronic transformers 60-100 VA (230 V) - 60-500 VA (127 V) for halogen lamps with ferromagnetic transformers Nominal plate dimensions: 86 x 86 mm</p> <p>1-gang 2-way</p>

Synergy™

double pole switches - white



7 301 10



7 300 22

Front plates: white thermoset
Terminal screws captive and backed off ready for cabling - large angled terminal entries
Compact mechanism for maximised wiring space
Supplied with faceplate screw caps

Pack	Cat.Nos	
10	7 300 10	<p>Double pole switches 20 A - 250 V~</p> <p>Conform to BS EN 60669-1 For flush-mounting, back box to be min. 25 mm deep Use cord outlet accessory box Cat.No 7 300 53 ASTA licence </p> <p>Nominal plate dimensions: 86 x 86 mm DP switch</p>
10	7 300 12	<p>DP switch + red LED power indicator LED invisible until activated</p>
10	7 301 10	<p>DP switch marked "WATER HEATER"</p>
10	7 301 12	<p>DP switch marked "WATER HEATER" + red LED power indicator LED invisible until activated</p>
10	7 300 22	<p>Double pole switches 45 A - 250 V~</p> <p>Conform to BS EN 60669-1 ASTA licence </p> <p>For flush-mounting, back box to be min. 45 mm deep Nominal plate dimensions: 86 x 86 mm</p> <p>DP switch</p>
10	7 300 23	<p>DP switch + red LED power indicator LED invisible until activated</p>
10	7 301 22	<p>DP switch red rocker marked "COOKER"</p>
5	7 300 20	<p>Nominal plate dimensions: 146 x 86 mm</p> <p>DP switch</p>
5	7 300 21	<p>DP switch + red LED power indicator LED invisible until activated</p>
5	7 301 20	<p>DP switch red rocker marked "COOKER"</p>