

Synergy™

telephone, data and TV sockets - white



7 300 50

7 300 57

7 300 43

Front plates: white thermoset
Terminal screws captive and backed off ready for cabling - large angled terminal entries
Compact mechanism for maximised wiring space
Supplied with faceplate screw caps

Pack	Cat.Nos	Euro module front plates
10	7 300 99	Suitable for use with standard 25 x 50 mm Euro data module inserts 1-gang - 86 x 86 mm 2 modules - aperture size 50 x 50 mm
10	7 301 00	2-gang - 86 x 146 mm 4 modules - aperture size 50 x 100 mm
Telephone sockets		
10	7 300 50	For flush-mounting, back box to be min. 35 mm deep Nominal plate dimensions: 86 x 86 mm UK master
10	7 300 51	UK secondary
10	7 300 54	RJ 11/RJ 12 - single
Data sockets		
1	7 300 56	Rapid cable connection For flush-mounting, back box to be min. 35 mm deep Nominal plate dimensions: 86 x 86 mm RJ 45 cat. 6 UTP - single
1	7 300 57	RJ 45 cat. 6 UTP - twin
TV sockets		
1	7 300 43	For DVBT, Cablecast and satellite installation UHD TV compatible Class A shielded star sockets LTE Ready (4G protected) Recommended coaxial cable: 17 VATC Star cabling (1 socket = 1 cable to antenna, splitter or multiswitch) Visual checking of the connection Meet EN 50083-4 and EN 50083-2 European directive TV: male connector (Ø9.5 mm) R: female connector (Ø9.5 mm) SAT: "F type" connector TV: 5-68 / 120-862 MHz R: 87.5-108 MHz SAT: 950-2400 MHz 2 modules For technical characteristics, see e-catalogue
1	7 300 43	Multi TV star sockets TV-R-SAT Low attenuation: < 1.5 dB
10	7 300 40	Single TV star sockets TV 9.5 mm male
1	7 300 41	TV "F" type

Synergy™

British standard socket outlets - white



7 300 65

7 300 79A

Front plates: white thermoset
Terminal screws captive and backed off ready for cabling - large angled terminal entries
Compact mechanism for maximised wiring space
Supplied with faceplate screw caps

Pack	Cat.Nos	Socket outlets 13 A - 250 V~
		Conform to BS 1363: Part. 2 For flush-mounting, back box to be min. 25 mm deep With safety shutter mechanism ASTA licence
		Options available as standard with red "power on" LED indicator Red LED "power on" upgrade pack also available
Unswitched		
10	7 300 65	1-gang Nominal plate dimensions: 86 x 86 mm
5	7 300 75	2-gang Nominal plate dimensions: 86 x 146 mm
Single pole - switched		
10	7 300 66	1-gang Nominal plate dimensions: 86 x 86 mm
5	7 300 76	2-gang Nominal plate dimensions: 86 x 146 mm
Single pole socket outlets 13 A - 250 V~ with USB charger		
		Conform to BS 1363-2 USB charger conform to IEC 60950-1
1	7 300 78A	1-gang - switched - USB Type-A - 3 A - 5 V_{DC} - 15 W Consumption in passive mode < 0.07 W
1	7 300 73A	1-gang - switched - USB Type-C - 18 W Fast charge feature: Power Delivery Consumption in passive mode < 0.07 W
1	7 300 79	2-gang - switched - USB Type-A + Type-C - 3 A - 5 V_{DC} - 15 W Consumption in passive mode < 0.08 W
Socket outlets 13 A - 250 V~ Special earth pin		
		With safety shutter mechanism For flush-mounting, back box to be min. 35 mm deep
Double pole - switched		
10	7 300 67	1-gang Nominal plate dimensions: 86 x 86 mm
5	7 300 77	2-gang Nominal plate dimensions: 86 x 146 mm