

Synergy™

double pole switches - Sleek Design



8 320 10



8 324 12



8 324 23

Sleek design

BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L

PSS: Plates made of Stainless Steel + rust resistance

GG: Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries

Compact mechanism for maximum wiring space

Pack	Cat.Nos	Double pole switches 20 A - 250 V~
		Conform to BS EN 60669-1 For flush-mounting, back box to be min. 35 mm deep Supplied with 1-gang side extension (3 mm thick) in case of extra wiring space needed Nominal plate dimensions: 86 x 86 mm
1	8 320 10	DP switch + blue LED power indicator
1	8 322 10	● Brushed stainless steel
1	8 324 10	● Polished stainless steel
		● Glossy gold
1	8 320 16	DP switch + cord outlet + blue LED power indicator
1	8 322 16	● Brushed stainless steel
1	8 324 16	● Polished stainless steel
		● Glossy gold
1	8 320 12	DP switches + blue LED power indicator
1	8 322 12	● Brushed stainless steel
1	8 324 12	● Polished stainless steel
		● Glossy gold

Pack	Cat.Nos	Double pole switches 45 A - 250 V~
		Conform to BS EN 60669-1 For flush-mounting, back box to be min. 47 mm deep Red rocker Nominal plate dimensions: 86 x 86 mm
1	8 320 23	DP switch + blue LED power indicator
1	8 322 23	● Brushed stainless steel
1	8 324 23	● Polished stainless steel
		● Glossy gold

Synergy™

British standard socket outlets and USB sockets - Sleek Design



8 320 75

Sleek design

BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L

PSS: Plates made of Stainless Steel + rust resistance

GG: Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries

Compact mechanism for maximum wiring space

Pack	Cat.Nos	Socket outlets 13 A - 250 V~
		Conform to BS EN 1363: Part. 2 With safety shutter mechanism For flush-mounting, back box to be min. 35 mm deep ASTA licence
		1-gang - unswitched
		Nominal plate dimensions: 86 x 86 mm
1	8 320 65	● Brushed stainless steel
1	8 322 65	● Polished stainless steel
1	8 324 65	● Glossy gold
		2-gang - unswitched
		Nominal plate dimensions: 86 x 146 mm
1	8 320 75	● Brushed stainless steel
1	8 322 75	● Polished stainless steel
1	8 324 75	● Glossy gold
		Single pole socket outlets 13 A - 250 V~
		Conform to BS EN 1363: Part. 2 With safety shutter mechanism For flush-mounting, back box to be min. 35 mm deep
		1-gang - switched
		Nominal plate dimensions: 86 x 86 mm
1	8 320 66	● Brushed stainless steel
1	8 322 66	● Polished stainless steel
1	8 324 66	● Glossy gold
		1-gang - switched with blue LED power indicator
		Nominal plate dimensions: 86 x 86 mm
1	8 320 67	● Brushed stainless steel
1	8 322 67	● Polished stainless steel
1	8 324 67	● Glossy gold
		2-gang - switched
		Nominal plate dimensions: 86 x 146 mm
1	8 320 76	● Brushed stainless steel
1	8 322 76	● Polished stainless steel
1	8 324 76	● Glossy gold
		2-gang - switched with blue LED power indicator
		Nominal plate dimensions: 86 x 146 mm
1	8 320 77	● Brushed stainless steel
1	8 322 77	● Polished stainless steel
1	8 324 77	● Glossy gold