



7 645 82A






7 645 88






7 645 11

Mechanisms supplied with cover plates and support frames in flow-pack
To be equipped with plates (p. 749)
Screw terminals
Fixing with screws or claws (supplied)

Pack	Cat.Nos	Motion sensors
1	7 645 83A 7 646 83A	<p>Compatible with any type of lamp IR detection. Detection field 170° Detection range 8 m Time delay setting from 5 s to 30 min Light level threshold setting from 5 to 1275 lux 4 levels of sensitivity setting Reduced depth: 25 mm</p> <p>Motion sensor, 2 wires, without neutral Standby consumption: 0.01W Accepted power by lamp type: - LEDs and CFL lamps: 2 to 100 W LED - Halogens, incandescent: 2 to 150 W - LEDs, CFLs, Halogen, fluo tube with ferromagnetic or electronic transformer: 2 to 150 VA If several sensors are installed on the same circuit, the minimum load changes: refer to the technical sheet Possibility to install up to 3 sensors in parallel Additional remote manual control possible with push button, 10 max. Can be associated with a modular time-lag switch (p. 106) Accepted power by lamp type will be power of the modular time-lag switch used Sensor without override</p> <p> ○ White ● Ivory</p> <p>Motion sensor, 3 wires, with neutral Standby consumption : 0.015 W Accepted power by lamp type: - LEDs and CFL lamps : 0 to 500 W LED - Compact fluorescent: 0 to 500W - Halogens, incandescent: 0 to 2000 W - LEDs, CFLs, Halogen, fluo tube with ferromagnetic or electronic transformer: 0 to 1000 VA Possibility to install up to 10 sensors in parallel Additional remote manual control possible with push button, 10 max. Master/Slave function available (10 slaves max. for 1 master) Sensor without override</p> <p> ○ White ● Ivory</p>
1	7 645 82A 7 646 82A	
1	7 645 88 7 646 88	<p>Rotary dimmers 300 W - 2-wire Equipped with overvoltage and short-circuit protection When switched on, gradually (2 seconds) light up at the level set before last switch-off Can be remotely controlled via non-illuminated push-buttons, with each push-button able to perform the ON/OFF and dimming function Screw terminals For all types of lamps : - dimmable LEDs: 5 to 75 W LED (10 lamps max.) - halogen with ferromagnetic or electronic transformer: 5 to 300 VA - fluorescent tube - ballast: 5 to 300 VA - halogen and incandescent 240 V~ : 5 to 300 W</p> <p> ○ White ● Ivory</p>

Mechanisms supplied with cover plates and support frames in flow-pack
To be equipped with plates (p. 749)
Screw terminals
Fixing with screws or claws (supplied)

Pack	Cat.Nos	Shutter controls
10 10	7 645 11 7 646 11	<p>Switches 3 positions (Raise / Stop / Lower) for direct motor control</p> <p> ○ White ● Ivory</p> <p>Push-buttons ○ White ● Ivory</p>
10 10	7 645 12 7 646 12	
1 1	6 647 93 6 648 93	<p>Keycard switches To operate the room's electrical circuits Turn off 30 seconds after the card is removed For cards of maximum 54 mm length Supplied without claws, add accessory Cat.No 6 650 99</p> <p> ○ White ● Ivory</p>
1 1	7 645 87 7 646 87	<p>Electronic room thermostat For direct radiant ceiling panels and underfloor heating Adjustment range: from 10 °C to 30 °C Frost protection 7 °C Adjustment precision: 0.5 °C 1 potential free N/O contact Switching capacity: 8 A - 250 V~ - resistive circuit 2 A - 250 V~ - inductive circuit Power supply: 230 V~ 50/60 Hz Adjustable brightness of LEDs Can be associated with a clock for comfort and eco mode</p> <p> ○ White ● Ivory</p>



Smarter connected thermostat
p. 867

