



Front plates: grey epoxy coated steel
Terminal screws captive and backed off ready for cabling - large angled terminal entries
Supplied complete with close fit 43 mm deep surface-mounting back box

Pack	Cat.Nos	Single pole plate switches 10 AX - 250 V~
5	7 338 00	Conform to BS EN 60669-1: 2000 Flush-mounting back box: min. 16 mm deep Nominal plate dimensions: 86 x 86 mm 1-gang 1-way 1-gang 2-way 1-gang intermediate
5	7 338 01	
5	7 338 05	
5	7 338 02	2-gang 2-way
5	7 338 03	3-gang 2-way
Double pole switches 20 A - 250 V~ Conform to BS EN 60669-1: 2000 Flush-mounting back box: min. 25 mm deep Nominal plate dimensions: 86 x 86 mm DP switch		
5	7 338 10	DP switch with cord outlet + red LED power indicator DP switch + red LED power indicator
5	7 338 16	
5	7 338 12	
Double pole switch 45 A - 250 V~ Conforms to BS EN 60669-1: 2000 Red rocker Flush-mounting back box: min. 48 mm deep Nominal plate dimensions: 146 x 86 mm DP switch + red power indicator		
5	7 338 21	

Pack	Cat.Nos	Television sockets
5	7 338 40	Flush-mounting back box: min. 35 mm deep Nominal plate dimensions: 86 x 86 mm Screened TV - single, male
1	7 338 41	Screened satellite - single, "F" type
Telephone sockets Flush-mounting back box: min. 35 mm deep Nominal plate dimensions: 86 x 86 mm		
5	7 338 50	Single master
5	7 338 51	Single secondary
Data sockets cat. 6 Rapid cable connection Flush-mounting back box: min. 35 mm deep Nominal plate dimensions: 86 x 86 mm RJ 45 - single		
1	7 338 56	
Blanking plates		
5	7 338 95	1-gang Nominal plate dimensions: 86 x 86 mm
5	7 338 96	2-gang Nominal plate dimensions: 86 x 146 mm
Cable outlet 20 A - 250 V~ Conforms to BS 5733: 1995 Flush-mounting back box: min. 25 mm deep Nominal plate dimensions: 86 x 86 mm 20 A - with terminal block and outlet gland		
5	7 338 19	