


**Living Now**

switches and push-buttons (continued)



BT-KW01A BT-KG01M2D BT-KM01F

Pack	Cat.Nos	Additional cover plates with symbols
10 10 10	BT-KW01A BT-KG01A BT-KM01A	<p>2-module cover plates can be mounted on a 1-module mechanism by associating the mechanism with 2 half-modules Cat.No BT-K4949 (p. 776) With transparent symbol allowing the backlighting of the function on the cover plate</p> <p><b>With light symbol - 1 module</b></p> <ul style="list-style-type: none"> <li>○ White</li> <li>● Black</li> <li>● Sand</li> </ul>
10 10 10	BT-KW01M2A BT-KG01M2A BT-KM01M2A	<p><b>With light symbol - 2 modules</b></p> <ul style="list-style-type: none"> <li>○ White</li> <li>● Black</li> <li>● Sand</li> </ul>
10 10 10	BT-KW01D BT-KG01D BT-KM01D	<p><b>With bell symbol - 1 module</b></p> <ul style="list-style-type: none"> <li>○ White</li> <li>● Black</li> <li>● Sand</li> </ul>
5 5 5	BT-KW01M2D BT-KG01M2D BT-KM01M2D	<p><b>With bell symbol - 2 modules</b></p> <ul style="list-style-type: none"> <li>○ White</li> <li>● Black</li> <li>● Sand</li> </ul>
10 10 10	BT-KW01F BT-KG01F BT-KM01F	<p><b>With key symbol - 1 module</b></p> <ul style="list-style-type: none"> <li>○ White</li> <li>● Black</li> <li>● Sand</li> </ul>
5 5 5	BT-KW01M2F BT-KG01M2F BT-KM01M2F	<p><b>With key symbol - 2 modules</b></p> <ul style="list-style-type: none"> <li>○ White</li> <li>● Black</li> <li>● Sand</li> </ul>

**Living Now**

dimmers and motion sensors



BT-K4411 BT-K4430 BT-K4431

Cover plates selection chart p. 754  
Plates selection chart p. 778

To be equipped with a support frame, a cover plate and a plate

Pack	Cat.Nos	Dimmer push-button
1	BT-K4411	<p>Can be remotely controlled via non-illuminated push-buttons, with each push-button able to perform the dimming function. When switched on, lightens at the level set before last switched off</p> <p><b>Universal dimmer without neutral, 2-wire</b></p> <p>2 modules. For all types of lamps:</p> <ul style="list-style-type: none"> <li>- dimmable LEDs: 3 W to 75 W (10 lamps max.)</li> <li>- dimmable compact fluorescent lamps: 3 W to 75 W (10 lamps max.)</li> <li>- halogen with ferromagnetic or electronic transformer: 3 VA to 400 VA</li> <li>- fluorescent tube - ballast: 3 VA to 200 VA</li> <li>- halogen and incandescent: 3 W to 400 W</li> </ul> <p>Functioning:</p> <ul style="list-style-type: none"> <li>- dimming function</li> <li>- pre-set level mode (0%, 33%, 66% and 100%)</li> <li>- nightlight mode (dimming down of the lamp for 1 hour)</li> </ul>
1	BT-K4410	<p><b>Dimmer switch with neutral, for 0-10 V ballast</b></p> <p>2 modules For lamps with 0-10 V ballast Maximum loads: 20 VA to 600 VA</p>
1	BT-K4430	<p><b>Motion sensors</b></p> <p>IR detection. Compatible with all types of lamps Detection field: 120°. Detection range: 8 m</p> <p><b>2-wire motion sensor, without neutral</b></p> <p>2 modules. Accepted power by lamp type:</p> <ul style="list-style-type: none"> <li>- LEDs and compact fluorescent: 3 to 100 W</li> <li>- LEDs, CFLs, halogen, fluo tubes with ferromagnetic or electronic transformer: 3 to 250 VA</li> </ul> <p>- Halogen 230 V, incandescent: 3 to 250 W</p> <p>If several sensors are installed on the same circuit, the minimum load changes; refer to technical sheet Possibility to install up to 3 sensors in parallel Time delay setting from 10 s to 10 min. Light level threshold setting from 5 lux to 1275 lux. Standby consumption: 0.02 W. Can be used with or without override depending on the cover plate selected</p>
1	BT-K4432	<p><b>3-wire motion sensors, with neutral, without override</b></p> <p>2 modules. Accepted power by lamp type:</p> <ul style="list-style-type: none"> <li>- LEDs and compact fluorescent: 0 to 50 W</li> <li>- LEDs, CFLs, halogen with ferromagnetic or electronic transformer: 0 to 200 VA</li> <li>- Fluo tubes with ferromagnetic or electronic transformer: 0 to 150 VA</li> </ul> <p>- Halogen 230 V, incandescent: 0 to 400 W</p> <p>Only 1 sensor per circuit. Time delay setting from 10 s to 10 min. Light level threshold setting from 5 lux to 1275 lux. Standby consumption: 0.55 W</p>
1	BT-K4431	<p>1 module. Accepted power by lamp type:</p> <ul style="list-style-type: none"> <li>- LEDs and compact fluorescent: 0.5 to 50 W</li> <li>- LEDs, CFLs, halogen with ferromagnetic or electronic transformer: 2 to 460 VA</li> <li>- Fluo tubes with ferromagnetic or electronic transformer: 2 to 460 VA</li> </ul> <p>- Halogen 230 V, incandescent: 2 to 460 W</p> <p>Only 1 sensor per circuit. Time delay setting from 30 s to 10 min</p>