

Niloé™

USB charging sockets



7 645 94



7 645 97

Mechanisms supplied with support frames and cover plates
To be equipped with plates (p. 749)
Fixing with screws or claws (supplied)
For installation in flush-mounting box depth 40 mm minimum
Supplied cordless


Pack	Cat.Nos	Double USB Type-A charging sockets
1	7 645 94	5 V - 3 A - 15 W For recharging portable device Surge protection > 1 kV Consumption in passive mode < 0.06 W Power supply AC/DC efficiency at highest Level (VI) 2x2.5 mm ² screw terminals Class II SELV Supplied cordless Double USB sockets 2 modules For fast charging smartphones and tablet PC ○ White ● Ivory
1	7 646 94	
1	7 645 93	USB Type-C charging sockets Universal charger for smartphones and fast charging table PC Surge protection > 1 kV Consumption in passive mode < 0.07 W Power supply AC/DC efficiency at highest Level (VI) 2x2.5 mm ² screw terminals Class II SELV Supplied cordless 2 modules Single 5 V - 1.5 A - 7.5 W ○ White
1	7 645 95	Double 5 V - 3 A - 15 W ○ White ● Ivory
1	7 646 95	
1	7 645 97	Double USB Type-A / USB Type-C charging sockets 5 V - 3 A - 15 W Surge protection > 1 kV Consumption in passive mode < 0.07 W Power supply AC/DC efficiency at highest Level (VI) 2x2.5 mm ² screw terminals Class II SELV Supplied cordless 2 modules For fast charging smartphones and tablet PC ○ White ● Ivory
1	7 646 97	

Niloé™

RJ 45, telephone and loudspeaker sockets



7 645 75



7 645 76



7 645 70

Mechanisms supplied with support frames and cover plates
To be equipped with plates (p. 749)
Fixing with screws or claws (supplied)

Pack	Cat.Nos	Cat.6 sockets
10	7 645 77	RJ 45 sockets ○ White - FTP ○ White - STP ○ White - UTP 9-contact ● Ivory - UTP 9-contact
10	7 645 75	
10	7 645 73	
10	7 646 73	
10	7 645 78	2xRJ 45 sockets ○ White - FTP ○ White - STP ○ White - UTP 9-contact ● Ivory - UTP 9-contact
10	7 645 76	
10	7 645 74	
10	7 646 74	
10	7 645 71	Cat.5 sockets RJ 45 sockets - 360° shielded ○ White - UTP ● Ivory - UTP
10	7 646 71	Telephone sockets RJ 11 sockets ○ White ● Ivory
10	7 645 69	RJ 11 + RJ 45 Cat.5 UTP sockets ○ White ● Ivory
10	7 646 69	
10	7 645 70	Double loudspeaker socket ○ White
10	7 646 70	
10	7 645 81	