



Cover plates selection chart **p. 755-764**
Plates selection chart **p. 778**

To be equipped with a support frame, a cover plate and a plate

Pack	Cat.Nos	Reading light
1 1 1	BT-KW4362 BT-KG4362 BT-KM4362	<p>Fitted with maintenance-free LEDs LED colours: 3000 K (neutral white) 230 V power supply - energy Class A Screw terminals For installation in the bedhead Offers directional lighting (on/off and dimming) Equipped with a flexible cable so the head can swivel Built-in dimmer Consumption: 3.3 W Luminous flux 110 lumen (equivalent to 15 W incandescent) Service life 40000 hours 1 module For installation in flush-mounting box</p> <p>○ White ● Black ● Sand</p>
1	BT-K4380	<p>Torch and safety LED lamp</p> <p>Removable and rechargeable torch Lights up automatically when there is a power cut Push&pull pull-out system complete with recharge base White LED light with high luminous efficiency On/off switch and Spot push-button to increase the brightness when necessary Interchangeable Ni-MH batteries without "memory" effect - 2-hour service life Standby consumption: 0.4 W 230 V~ power supply 2 modules Spare batteries for removable torch</p>
1	BT-4380NB	<p>LED safety lamp With automatic operation when there is a power cut 230 VA 50/60 Hz Power consumption: 2.5 VA (0.1 W) Rechargeable non-replaceable NiMH 3.6 V 140 mAh battery - complete charge in 48 hours - 2-hour service life Maximum cable section 1 x 1.5 mm² Light intensity: 2400 mcd 1 module</p>
10 10	BT-K4382 BT-K4382V12V24	<p>Step marker lamps 2 modules Fitted with maintenance-free LEDs LED colours: 3000 K (neutral white) Energy Class A On/off switch - 0.15/0.5 W Screw terminals. For installation in flush-mounting box 127/230 V~ power supply 12/24 V~ power supply</p>

Cover plates selection chart **p. 755**
Plates selection chart **p. 778**

Pack	Cat.Nos	Roller blind controls 6 A - 250 V~
10	BT-K4027	<p>To be equipped with a support frame, a cover plate and a plate</p> <p>Switch For direct control of blind, awning or canopy motor 1 module Can be equipped with a 2-module cover plate by associating the mechanism with 2 half-modules Cat.No BT-K4949 (p. 776)</p>
10	BT-K4037N	<p>Push-button For direct control of roller blinds 1 module Can be equipped with a 2-module cover plate by associating the mechanism with 2 half-modules Cat.No BT-K4949 (p. 776)</p>
5 5 5	BT-KW06V BT-KG06V BT-KM06V	<p>Additional cover plates for roller blind control Cat.No BT-K4027</p> <p>For vertical installation - 1 module ○ White ● Black ● Sand</p>
5 5 5	BT-KW06M2V BT-KG06M2V BT-KM06M2V	<p>For vertical installation - 2 modules ○ White ● Black ● Sand</p>
5 5 5	BT-KW05V BT-KG05V BT-KM05V	<p>Additional cover plates for roller blind control Cat.No BT-K4037N</p> <p>For vertical installation - 1 module ○ White ● Black ● Sand</p>
5 5 5	BT-KW05M2V BT-KG05M2V BT-KM05M2V	<p>For vertical installation - 2 modules ○ White ● Black ● Sand</p>