

## LED Twinspot emergency lighting luminaires




High performance LED non maintained emergency lighting luminaires  
 Certified to IEC and EN 60598-2-22 standards  
 High power LEDs spotlights with optimized lighting distribution  
 Low consumption electronic switching power supply  
 High capacity terminals: 2 x 2.5 mm<sup>2</sup>  
 IP 55 - IK 07  
 Duration: 1, 2 and 3 hours  
 Ni-Cd batteries  
 Recharge time: 24h  
 Green charge indicator with high luminosity LED, to improve visibility from the floor when high installation  
 Power supply: 230 V $\sim$   $\pm$  10% - 50/60 Hz  
 Class II  $\square$   
 Rest mode with remote control device Cat.No 0 039 01 (p. 914) to avoid battery discharge in case of voluntary power cut  
 Surface-mounting installation with 4 wall-mounting lugs (Cat.No 0 358 02, supplied) or 4 screws (not supplied)

Pack	Cat.Nos	Standard LED spotlight luminaires - Non-Maintained (NM)
1	6 614 50	Require normal lighting manual switching OFF, in order to test emergency lighting mode 2 x 300 lm - 1h
1	6 614 51	2 x 450 lm - 1h
1	6 614 52	2 x 750 lm - 1h
1	6 614 53	2 x 1250 lm - 1h
1	6 614 54	2 x 500 lm - 2h
1	6 624 52	<b>Autotest &amp; addressable LED spotlight luminaire - Non-Maintained (NM)</b> 2 x 750 lm - 1h Incorporates an automatic self-testing system that checks periodically the emergency lighting function: - weekly test of emergency lighting mode - quarterly test of battery duration Tests result is visible via 2 signalling LEDs (green = OK and yellow = defective) on the luminaire Addressable function is activated by setting an ID on each luminaire with infrared configuration tool (Cat.No 0 626 10) (p. 916) and wiring a complementary BUS line Operating state of all addressable luminaires can be centralized by the control interface Cat.No 0 626 00 (p. 916) and monitored on a local touch screen controller (Cat.No 0 626 01), or with the building's plan on Legrand Vision System (L.V.S. 2) PC software


## LED Twinspot emergency lighting luminaires

### ■ Dimensions

Cat.Nos 6 614 50/51/52/54



Cat.No 6 614 53



Cat.No 6 624 52

