DLPlus mini-trunking 20 x 12.5 and 32 x 12.5

profiles and finishing accessories



Selection chart **p. 1043**
Wiring capacity chart **p. 1048**

Mini-trunking

Pack	Cat.Nos 20 x 12.5	Cat.Nos 32 x 12.5	
			EN 50085-2-1 approved
			Without central partition
			Mini-trunking with cable grip
			Equipped with an integrated device for holding cables in place
120[1] | 80	0 300 08	0 300 15	Length 2.10 m
120[1]	6 489 05		Without adhesive
			With adhesive
			With central partition
120[1] | 80[1]	0 300 07	0 300 14	Length 2.10 m



Finishing accessories

Pack	Cat.Nos 20 x 12.5	Cat.Nos 32 x 12.5	
20	0 312 02	0 312 03	End cap
10	0 302 21	0 302 51	Changeable internal-external angle
10	0 302 23	0 302 53	Changeable flat angle
20	0 336 02	0 336 03	Cover joint
10	0 302 24	0 302 54	Flat T-junction

1: Number of metres in pack

Special frames

Pack	Cat.Nos	
		Supplied with end cap and divider for separation of currents
		Installation alongside the mini-trunking
		For vertical or horizontal mounting of surface-mounting wiring accessories (p. 1049)
10	0 314 04	1 gang
5	0 314 14	2 gang

Adaptors

Pack	Cat.Nos	
		Adaptor for mounting Mosaic frames at end of the mini-trunking
10	0 316 40	For 20 x 12.5 mini-trunking
10	0 316 41	For 32 x 12.5 mini-trunking
		Adaptor for mounting Mosaic frames alongside the mini-trunking
10	0 317 01	For Mosaic frames Cat.No 0 316 11 (p. 1047)
10	0 317 02	For Mosaic frames Cat.Nos 0 316 13 and 0 316 21 (p. 1047)
5	0 317 03	For Mosaic frames Cat.Nos 0 316 14 and 0 316 22 (p. 1047)

Connection of luminaires **p. 1047**

Other frames for wiring accessories **p. 1047**

Surface-mounting wiring accessories **p. 1049**