

# Keor multiplug

Line interactive UPS 600 and 800 VA



3 100 81

Pack	Cat.Nos	UPS												
		Automatic start-up: when there is no mains supply or it is of poor quality, the UPS continues working using a battery and switches off if the network breaking time exceeds the back-up time Technical characteristics - Replaceable fuse for fine protection in case of short-circuits - LED indicators - Internal AVR (Automatic Voltage Regulator) - USB Charger												
		<b>German standard output sockets</b>												
		<table border="1"> <thead> <tr> <th>Nominal power (VA)</th> <th>Active power (W)</th> <th>Back-up time (min)</th> <th>No. of sockets</th> </tr> </thead> <tbody> <tr> <td>600</td> <td>360</td> <td>up to 15</td> <td>4 + 2</td> </tr> <tr> <td>800</td> <td>480</td> <td>up to 15</td> <td>4 + 2</td> </tr> </tbody> </table>	Nominal power (VA)	Active power (W)	Back-up time (min)	No. of sockets	600	360	up to 15	4 + 2	800	480	up to 15	4 + 2
Nominal power (VA)	Active power (W)	Back-up time (min)	No. of sockets											
600	360	up to 15	4 + 2											
800	480	up to 15	4 + 2											
		<b>French standard output sockets</b>												
		<table border="1"> <thead> <tr> <th>Nominal power (VA)</th> <th>Active power (W)</th> <th>Back-up time (min)</th> <th>No. of sockets</th> </tr> </thead> <tbody> <tr> <td>600</td> <td>360</td> <td>up to 15</td> <td>4 + 2</td> </tr> <tr> <td>800</td> <td>480</td> <td>up to 15</td> <td>4 + 2</td> </tr> </tbody> </table>	Nominal power (VA)	Active power (W)	Back-up time (min)	No. of sockets	600	360	up to 15	4 + 2	800	480	up to 15	4 + 2
Nominal power (VA)	Active power (W)	Back-up time (min)	No. of sockets											
600	360	up to 15	4 + 2											
800	480	up to 15	4 + 2											

NOTE: The stated back-up times in minutes are estimated and may vary according to the load characteristics, operating conditions and environment

# Keor multiplug

technical characteristics

## Technical characteristics

Cat.Nos	3 100 81/83	3 100 82/84
<b>General characteristics</b>		
Nominal power (VA)	600	800
Active power (W)	360 - 480	
Technology	Line interactive VI	
Waveform	Pseudo-sinusoidal	
<b>Input characteristics</b>		
Nominal voltage	230 V	
Input voltage range	170 - 290 V	
AC power protection	Fuse	
Nominal frequency	50 - 60 Hz ± 5 Hz	
<b>Output characteristics</b>		
Battery mode voltage	230 V ± 10%	
Battery mode frequency (nominal)	50/60 Hz ± 1 Hz	
Pure Xll capacitance load	1.2 µF	
USB charger / Voltage	Type A female / 5 V	
Transfer time	2 to 6 ms typical	
<b>Batteries</b>		
Battery range type/voltage	12 V, 7 Ah	12 V, 7 Ah
Recharge time	4-6 hours (to 90% capacity)	
<b>Mechanical characteristics</b>		
Dimensions H x W x D (mm)	190 x 89.5 x 296	
Net weight (kg)	5	5.5
<b>Ambient conditions</b>		
Ambient operating temperature (°C)	0 to 40 °C	
Relative humidity (%)	< 95 % non-condensing	
Noise at 1 m (dBA)	Line mode	< 40
<b>Certifications</b>		
Reference product standards	EN 62040-1, EN 62040-2	

## 600-800 VA

