


Flush version floor boxes for raised or concrete floor



Selection charts **p. 1138-1139**
 Technical characteristics **p.1146-1147**

Conform to standard IEC/EN 60670-23
 Particularly suitable for tiled or marble floors

Pack	Cat.Nos	Support kits for floor boxes
		To be equipped with Mosaic or Arteor sockets Equipped with support frames for wiring accessories For sockets in horizontal position - adjustable height Can be installed directly in the raised floor For concrete floors, use auto-adjusting backboxes Cat.Nos 0 880 90/91/92 (p. 1151) or universal adjustable backbox Cat.No 0 880 80 (p. 1152) and adaptors Cat.Nos 0 880 81/82/83
1	0 881 20	12 (3 x 4) modules
1	0 881 21	18 (3 x 6) modules
1	0 881 22	24 (3 x 8) modules
		For sockets in vertical position For raised floors, use electrical insulation kits Cat.Nos 0 880 26/27/28 For concrete floors, use auto-adjusting backboxes Cat.Nos 0 880 90/91/92 (p. 1151) or universal adjustable backbox Cat.No 0 880 80 (p. 1152) and adaptors Cat.Nos 0 880 81/82/83
1	0 881 23	8 (2 x 4) modules
1	0 881 24	12 (2 x 6) modules
1	0 881 25	16 (2 x 8) modules
		Mounting adaptors for concrete floor For floor boxes (standard or flush version) Mounted on universal adjustable backbox Cat.No 0 880 80 (p. 1152)
1	0 880 81	8/12 modules - Cat.Nos 0 880 20/23/39 and 0 881 20/23/39
1	0 880 82	12/18 modules - Cat.Nos 0 880 21/24/40 and 0 881 21/24/40
1	0 880 83	16/24 modules - Cat.Nos 0 880 22/25/41 and 0 881 22/25/41
		Electrical insulation kits for raised floor
1	0 880 26	For 8 (2 x 4) module kits Cat.Nos 0 880 23 and 0 881 23
1	0 880 27	For 12 (2 x 6) module kits Cat.Nos 0 880 24 and 0 881 24
1	0 880 28	For 16 (2 x 8) module kits Cat.Nos 0 880 25 and 0 881 25

Pack	Cat.Nos	Kits for access covers
		Can be installed directly in the raised floor For concrete floors, use auto-adjusting backboxes Cat.Nos 0 880 90/91/92 (p. 1151) or universal adjustable backbox box Cat.No 0 880 80 (p. 1152) and adaptors Cat.Nos 0 880 81/82/83
1	0 881 39	For lid 8/12 modules - Cat.Nos 0 881 03/06
1	0 881 40	12/18 modules - Cat.Nos 0 881 04/07
1	0 881 41	16/24 modules - Cat.Nos 0 881 05/08
		Set of feet for H > 122 mm
1	0 881 42	4 screw-on feet For support kits Cat.Nos 0 881 20/21/22/23/24/25/39/40/41 Fitted instead of the original feet
		Lids for floor boxes (flush version) Installed on floor box support kits
		Metal lids with stainless steel coating For floor box:
1	0 881 03	8/12 modules - Cat.Nos 0 881 20/23/39
1	0 881 04	12/18 modules - Cat.Nos 0 881 21/24/40
1	0 881 05	16/24 modules - Cat.Nos 0 881 22/25/41
		Metal lids with brass coating
1	0 881 06	8/12 modules - Cat.Nos 0 881 20/23/39
1	0 881 07	12/18 modules - Cat.Nos 0 881 21/24/40
1	0 881 08	16/24 modules - Cat.Nos 0 881 22/25/41
		Finishing plates
		Stainless steel finish
1	0 881 45	8/12 modules
1	0 881 46	12/18 modules
1	0 881 47	16/24 modules
		Brass finish
1	0 881 48	8/12 modules
1	0 881 49	12/18 modules
1	0 881 50	16/24 modules