

## Mosaic™ mechanisms

### colour-lighting management



## Mosaic™ mechanisms

### timer switch and programmable time switch



Selection chart for boxes, supports and plates **p. 1198-1199**

Pack	Cat.Nos	Colour-lighting dimmers
1	0 784 03	<p>Allow the user to create lighting ambiances For (LEDs) DALI ballasts and drivers For controlling max. 21 RGB (Red/Green/Blue) luminaires Configuration via "learn" button Ideal for show-rooms, shops, restaurants, hotels, beauty salons... Work with power supply Cat.No 0 035 15 White</p> <p><b>Dimmer - 1 area</b> Allows manual change of colours and adjustment of light intensity and saturation</p>
1	0 035 13	<p><b>DALI power supplies</b> Work with colour-lighting dimmers Cat.Nos 0 784 03 and 0 488 60 230 V - 200 mA - 16 V 2 modules DIN For installation in false ceiling</p>
1	0 035 15	

Selection chart for boxes, supports and plates **p. 1198-1199**

Pack	Cat.Nos	Timer switch
1	0 784 20	<p>Interference suppression conforming to standard EN 55022 For timer control of a circuit with the following loads: - 1000 W 230 V~ incandescent and halogen - 1840 W resistive (heating) - 400 VA fluorescent and ELV halogen It is possible to install a number of timer switches in parallel on the same circuit 2-wire installation in 40 mm min. box Has an integrated LED. 2 modules</p> <p> ○ White</p>
1	0 784 25	<p><b>Programmable time switch</b> 20 hours working reserve Capacity: 8 weekly programmes Temporary or permanent override 1 output - 6 A - 250 V~ cos <math>\phi</math> = 1 1 changeover contact Used to programme the control of a circuit with the following loads: - 1200 W 230 V~ incandescent and halogen - 1800 VA fluorescent <math>\varnothing</math>26 or 38 mm and ELV halogen with ferromagnetic or electronic transformer - 1800 W motors (ventilation only) - 3600 W resistive (heating only)</p> <p> ○ White</p>