

## Mosaic™ mechanisms

USB data sockets, USB extender and SUB D socket




Selection chart for boxes, supports and plates p. 1198-1199

Pack	Cat.Nos	USB data sockets - for data transfer
1	0 787 46	<p>For connecting USB devices (scanner-printer, external hard disk) Max. cable length: 5 m. Recommended cable: USB A 1 module</p> <p><b>Preterminated - USB 2.0</b> Max. cable length: 5 m Equipped with a 15 cm cord ○ White</p> <p><b>Connection via screw terminals - USB 2.0</b> Max. cable length: 5 m USB 2.0. Cross-section: 1 mm<sup>2</sup> ○ White</p>
1	0 787 48	<p><b>USB extender - for data transfer</b></p> <p>For connecting USB devices (digital school board / interactive whiteboard...) located more than 5 m away (30 m max.) from a source (computer...) The kit includes a transmitter (1 module) and a receiver (1 module). The link between the transmitter and the receiver is made via a RJ 45 / RJ 45 cord ○ White</p>
1	0 787 65	<p><b>SUB D socket - 2 modules</b></p> <p>9 contacts - Screw terminals connection to link type RS 232 series</p>

## Mosaic™ mechanisms

audio and video sockets and USB extender

### Installation principle for preterminated HDMI type A socket Cat.No 0 787 78 (p. 1193)




HDMI cable

### Installation principle for USB extender - for data transfer Cat.No 0 787 48



USB Type-A male / USBType-A male cable  
 RJ 45/RJ 45 U/UTP or F/UTP Cat. 5e ou 6 cord

### Installation principle for preterminated HD15 socket Cat.No 0 787 77 (p. 1193)



Cordon HD15