


Mosaic™ mechanisms

illuminated signage functions, bulkhead lights, indicator lights and downlighter



Preprinted labels available in e-catalogue

Selection chart for boxes, supports and plates **p. 1198-1199**

All the illuminated functions are equipped with very low consumption LEDs with an estimated service life of 100,000 hours

Pack	Cat.Nos	Product Name	Description
		Illuminated signs 230 V~	
			Mechanisms integrating LEDs and a pivoting window that can take preprinted labels (available in the e-catalogue) Customised labels can be printed using a simple text editor Supplied with transparent paper to personalize labels
5	0 785 20		Signs with white LEDs - 2 modules A choice of 2 power levels (0.2 W or 1 W)
5	0 785 21		Signs with blue LEDs - 2 modules A choice of 2 power levels (0.2 W or 1 W)
5	0 785 24		Signs with 2-state LEDs with choice of green or red configurable on the mechanism (1 W) - 2 modules
1	0 785 22		Signs with white LEDs (1 W) 5 modules
1	0 785 23		Signs with blue LEDs (1 W) 5 modules
		Self-contained pilot light	
1	0 785 12		During a power failure, automatically gives light using a high power white LED (stand-alone operation: 1 hour) Circular lighting by blue LED in standby mode - 2 modules Supplements the regulatory safety lighting system to meet high requirements (for child care centres, health, accessibility, retirement homes, etc.) Option of switching off by remote control
		Skirting light with motion sensor	
1	0 785 11		Mechanism equipped with an infrared detection cell and a LED beam To be installed close to the floor (next to a socket for example) When someone passes, the mechanism detects movement and switches the light on Ideal to illuminate a corridor at night without dazzling people, or to highlight possible danger Equipped with an audible signal that can be deactivated
		Bulkhead pilot light	
1	0 785 10		To be installed in skirting trunking or bedhead strip 230 V - 2 modules White antimicrobial ⁽¹⁾
		Bulkheads	
			2 modules 12-24 V~ / = - 0.6 W
10	0 785 60		● Red
10	0 785 61		○ White
10	0 785 62		● Green
10	0 785 63		● Blue
			230 V~ (0.2 or 1 W)
10	0 785 70		● Red
10	0 785 71		○ White
10	0 785 72		● Green
10	0 785 73		● Blue
		Indicator lights	
			1 module For indicator or illuminated functions. Supplied with 4 coloured labels (red, orange, green and blue) Single indicator 230 V (1 W) - Antimicrobial ⁽¹⁾
10	0 785 01		
10	0 785 02		Double indicator 230 V (1 W) Antimicrobial ⁽¹⁾
10	0 785 51		Single indicator 12-24 V (0.2 W) Antimicrobial ⁽¹⁾
10	0 785 52		Double indicator 12-24 V (0.2 W) Antimicrobial ⁽¹⁾

⁽¹⁾: Contains a silver compound to prevent the growth of bacteria on the surface of the plate