




Rigid cover DLP-S snap-on and universal trunking

Technical characteristics



- Resistance to impact for installation and application: 2.0J
- Minimum storage and transport temperature: - 25 °C
- Minimum installation and usage temperature: - 5 °C
- Maximum application temperature: + 60 °C
- Resistance to flame propagation: Non-flame propagating
- Without electrical continuity characteristic
- With electrical insulating characteristic
- Degrees of protection: IP 40
- Rated current: 500 V
- Against mechanical shocks: IK 07

Wiring capacity

Rigid cover snap-on trunking

Dimensions	Cross-section per comp. (mm ²)	Capacity	Max. number of conductors (of the same type)			Cable Ø max. (mm)	
			3 x 1.5 mm ²	3 x 2.5 mm ²	UTP & FTP cat. 6 (mm)		
85 x 50 Cat.No 6 380 20 	1	2940	Max.	26	19	58	36
		2092	With 2P+E socket	18	13	41	
		2618	With RJ 45 socket	23	17	52	
100 x 50 Cat.No 6 380 30 	1	4146	Max.	36	27	82	36
		2738	With 2P+E socket	24	17	54	
		3264	With RJ 45 socket	29	21	65	
130 x 50 Cat.No 6 380 40 	1	2646	Max.	23	17	52	36
		1256	With 2P+E socket	11	8	25	
		1762	With RJ 45 socket	15	11	35	
	2	2616	Max.	23	17	52	
		1206	With 2P+E socket	10	7	24	
		1732	With RJ 45 socket	15	11	34	

Rigid cover universal trunking

Dimensions	Cross-section per comp. (mm ²)	Capacity	Max. number of conductors (of the same type)			Cable Ø max. (mm)	
			3 x 1.5 mm ²	3 x 2.5 mm ²	UTP & FTP cat. 6 (mm)		
100 x 50 Cat.No 6 380 38 	1	4224	Max.	47	33	172	40
190 x 50 Cat.No 6 380 50 	1	4017	Max.	45	29	164	40
	2						

Installation principle for fixing clip

