








# cavity floor service outlet boxes

## selection chart

No. of compartments	
<b>Floor box base</b>	
<b>Depth</b> 	Cavity floor box base – 75 mm deep Cavity floor box base – 85 mm deep Cavity floor box base – 110 mm deep
<b>Outlet plates</b>	
<b>13 A standard</b> 	13 A twin switched socket plate 13 A twin unswitched socket plate 13 A twin switched clean earth socket plate 13 A triple unswitched socket plate 13 A triple unswitched clean earth socket plate
<b>13 A non-standard</b> 	13 A twin NS switched socket plate 13 A twin NS switched clean earth socket plate
<b>RCD 30 mA passive</b> 	2 gang RCD socket plate 2 gang RCD socket plate – clean earth
<b>Data</b> 	37 x 22 mm – 2 cut-out plate 37 x 22 mm – 4 cut-out plate 37 x 22 mm – 4 cut-out wave plate 37 x 22 mm – 6 cut-out plate 47.5 x 23.5 mm – 4 cut-out plate
<b>General</b> 	2 x standard single outlet 60.3 mm Standard 2 gang outlet plate 120.6 mm 51 x 51 mm – 1 cut-out plate 51 x 51 mm – 2 cut-out plate Blank plate 58 x 53.5 mm – 1 cut-out plate to accept Arteor mounting frame <sup>1</sup> 58 x 53.5 mm – 2 cut-out plate to accept 2 x Arteor mounting frames <sup>1</sup>
<b>Lids and trims</b>	
	ABS with carpet trim – 6 mm recess Combination with edge trim – 6 mm recess Metal, powder coated with carpet trim – 8 mm recess (RAL 7024) Metal, powder coated with edge trim – 8 mm recess (RAL 7024) Stainless steel with carpet trim – 8 mm recess (Satin) Stainless steel with edge trim – 8 mm recess (Satin) Brass with carpet trim – 8 mm recess (Polished) Brass with edge trim – 8 mm recess (Polished)

1 : For Arteor mounting frames, refer to the latest Wiring Devices catalogue

	1 compartment	2 compartment	3 compartment	4 compartment
	–	CAV275	CAV375	CAV475
	CAV185	CAV285	CAV385	CAV485
	–	CAV2110	CAV3110	CAV4110
	SP3201	SP3201	SP3201	SP4201
	SP3200	SP3200	SP3200	SP4200
	SP3211	SP3211	SP3211	SP4211
	SP3300	SP3300	SP3300	SP4300
	SP3310	SP3310	SP3310	SP4310
	SP3221	SP3221	SP3221	SP4221
	SP3231	SP3231	SP3231	SP4231
	SP3202	SP3202	SP3202	SP4202
	SP3212	SP3212	SP3212	SP4212
	SP3203	SP3203	SP3203	SP4203
	SP3403	SP3403	SP3403	SP4403
	SP3404	SP3404	SP3404	SP4404
	SP3603	SP3603	SP3603	SP4603
	SP3408	SP3408	SP3408	SP4408
	SP3205	SP3205	SP3205	–
	SP3105	SP3105	SP3105	–
	SP3106	SP3106	SP3106	SP4106
	SP3206	SP3206	SP3206	SP4206
	SP3000	SP3000	SP3000	SP4000
	SP3107	SP3107	SP3107	SP4107
	SP3207	SP3207	SP3207	SP4207
	–	FBL2ABS	FBL3ABS	FBL3ABS
	–	FBL2COM	FBL3COM	FBL3COM
	FBL1MCT	FBL2MCT	FBL3MCT	FBL3MCT
	FBL1MET	FBL2MET	FBL3MET	FBL3MET
	FBL1SCT	FBL2SCT	FBL3SCT	FBL3SCT
	FBL1SET	FBL2SET	FBL3SET	FBL3SET
	FBL1BCT	FBL2BCT	FBL3BCT	FBL3BCT
	FBL1BET	FBL2BET	FBL3BET	FBL3BET